

## Key Features

HARDWARE BLUE LIGHT FILTER | FRAMELESS DESIGN |

ULTRA-WIDE VIEWING ANGLES | VERSATILE

CONNECTIVITY | FULL HD 1080P RESOLUTION



## Product Description

With flexible connectivity, wide-angle viewing, and amazing screen performance, the ViewSonic® VA2759-smh delivers solid multimedia features and a sleek design at a great value. Featuring SuperClear IPS panel technology, the 27" VA2759-smh delivers stunning brightness and contrast at nearly any viewing angle. A minimalistic design, edge-to-edge screen, and frameless bezel make this an ideal monitor for nearly seamless multi-screen setups. Whether for working at the office, or enjoying entertainment at home, the VA2759-smh also features an HDMI port for flexible connectivity to PCs, laptops, gaming consoles, and other multimedia devices. Flicker-Free technology and a Blue Light Filter help to minimize eyestrain from extended viewing periods. In addition, a 3-year limited warranty, along with one of the industry's best pixel performance policies, makes the VA2759-smh a great overall value choice.



- 1. VESA Compatible Mount 100 x 100mm
- 2. Menu Controls
- 3. AC In
- 4. 3.5mm Audio In
- 5. 3.5mm Audio Out

- 6. VGA
- 7. HDMI 1.4



27"  
DISPLAY



IPS  
PANEL



1920 x 1080  
RESOLUTION

### Contact Sales

- call: 888.881.8781
- email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)
- visit: [viewsonic.com](http://viewsonic.com)

#### Display:

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS
Resolution:	1920 x 1080
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	50,000,000:1
Light Source:	LED
Brightness:	250 cd/m2
Colors:	16.7M
Response Time (Typical GTG):	4ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30,000
Panel Surface:	Anti-glare, hard-coating (3H)

#### Compatibility:

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080

#### Connector:

3.5mm Audio In(1), 3.5mm Audio Out(1), HDMI In(1), VGA(1), Power in(3-pin plug (CEE22))

#### Audio:

Internal Speakers:	2-watt (x2)
--------------------	-------------

#### Power:

Eco Mode (Conserve):	11W
Eco Mode (optimized):	14W
Consumption (typical):	17W
Consumption (max):	25W
Voltage:	AC 100-240V (universal), 50-60Hz
Stand-by:	0.5W
Power Supply:	Internal

#### Additional Hardware:

Kensington Lock Slot:	1
-----------------------	---

#### Controls:

Physical Controls:	Key 1 (Favorite), Key 2, Key 3, Key 4, Key 5 (power)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

#### Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

#### Mount:

VESA Compatible:	100 x 100 mm
------------------	--------------

#### Video Signal:

Frequency Horizontal:	24 ~ 86 KHz
Frequency Vertical:	48 ~ 75 Hz

#### Video Input:

Analog Sync:	Separate Sync, Composite Sync, Sync on Green, TMDS
--------------	--

#### Ergonomics:

Tilt (Forward/Back):	5° / 22°
----------------------	----------

#### Weight (imperial):

Net (lbs):	9.7
Net Without Stand (lbs):	8.2
Gross (lbs):	13.2

#### Weight (metric):

Net (kg):	4.4
Net Without Stand (kg):	3.7
Gross (kg):	6.0

#### Dimensions (imperial) (WxHxD):

Packaging (in.):	27.4 x 18.4 x 5.7
Physical (in.):	24.2 x 17.5 x 9.3
Physical Without Stand (in.):	24.2 x 14.1 x 1.9

#### Dimensions (metric) (WxHxD):

Packaging (mm):	697.0 x 467.0 x 144.0
Physical (mm):	615.0 x 444.0 x 235.0
Physical Without Stand (mm):	615.0 x 358.0 x 48.0

#### General:

Regulations: cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT Silver, CEC, NOM, Mexico Energy, CB, RoHS

PACKAGE CONTENTS: VA2759-SMH x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, Quick Start Guide x1

Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.

Warranty: Three-year limited warranty on parts, labor and backlight

UPC: 766907837513

#### Accessories:

CB-00008948, CB-00009950, LCD-DMA-002, LCD-EE-27-03, LCD-EEEW-27-01, LCD-EEEW-27-02, LCD-EW-27-01, LCD-EW-27-02, LCD-EW-27-03, LCD-WMK-001, VSPF2700

#### Awards:

