

# 430 Series

## Small Mushroom Button Switches



SDC's 430 heavy duty industrial series incorporates a 1½" round mushroom button with heavy duty contacts. The assembly is capable of withstanding high impact and is ideal for heavy duty high frequency use.

**432K models latch when depressed and must be reset with the built-in-key.** Applications include alarm, panic alarm and emergency door release where systems are restored by authorized personnel only.



432KLDUR



### MODELS

- 431** Alternate Action (AA) On/Off, SPST
- 432** Momentary (MO), SPST
- 432K** Momentary (MO) Latching with Key Reset, DPST
- 434** Momentary (MO), DPST
- 435** Alternate Action (AA) On/Off, DPST



### STANDARD FEATURES

- 1½" mushroom exit switches
- Heavy duty to withstand impact
- Water resistant contacts
- Ideal for high frequency use
- Screw terminal wire connections
- Green button standard\*

\* Red button is standard for 432K models



### OPTIONAL FEATURES

- Red button
- Visual status indicator (LED)
- Alternative signage

## SPECIFICATIONS

	<b>431</b>	<b>432</b>	<b>432K</b>	<b>433</b>	<b>434</b>	<b>435</b>
<b>Faceplate</b>	20 Guage Stainless Steel	20 Guage Stainless Steel	20 Guage Stainless Steel	20 Guage Stainless Steel	20 Guage Stainless Steel	20 Guage Stainless Steel
<b>Button</b>	Green	Green	Red	Green	Green	Green
<b>Weight</b>	0.5 lbs	0.5 lbs	0.5 lbs	0.5 lbs	0.5 lbs	0.5 lbs
<b>Contact</b>	SPST	SPST	DPST	SPST	DPST	DPST
<b>Rating</b>	6 Amp @ 30 VDC Resistive	6 Amp @ 30 VDC Resistive	6 Amp @ 30 VDC Resistive	6 Amp @ 30 VDC Resistive	6 Amp @ 30 VDC Resistive	6 Amp @ 30 VDC Resistive
<b>Type</b>	Alternate Action (AA) On/Off	Momentary (MO)	Momentary (MO) Latching w/ Key Reset	Momentary (MO) w/ External Relock Timer	Momentary (MO)	Alternate Action (AA) On/Off
<b>Normally Closed (NC)</b>	<b>431C</b>	<b>432C</b>	-----	-----	-----	-----
<b>Normally Open (NO)</b>	<b>431O</b>	<b>432O</b>	-----	<b>433</b>	-----	-----
	<b>431CN</b> <b>431ON</b>	<b>432CN</b> <b>432ON</b>	<b>432KN</b>	-----	<b>434N</b>	<b>435N</b>
<b>Size</b>	Narrow	Narrow	Narrow	-----	Narrow	Narrow
<b>Dimensions</b>	1¾" x 4½"	1¾" x 4½"	1¾" x 4½"	-----	1¾" x 4½"	1¾" x 4½"
<b>Signage</b>	-----	EXIT	-----	-----	EXIT	-----
	<b>431C</b> <b>431O</b>	<b>432C</b> <b>432O</b>	<b>432K</b> <b>432KLD</b>	-----	<b>434</b>	<b>435</b>
<b>Size</b>	Single Gang	Single Gang	Single Gang	-----	Single Gang	Single Gang
<b>Dimensions</b>	2⅞" x 4½"	2⅞" x 4½"	2⅞" x 4½"	-----	2⅞" x 4½"	2⅞" x 4½"
<b>Signage</b>	-----	EXIT	LOCKDOWN*	-----	EXIT	-----
	-----	-----	-----	433	-----	-----
<b>Size</b>	-----	-----	-----	Double Gang	-----	-----
<b>Dimensions</b>	-----	-----	-----	4½" x 4½"	-----	-----
<b>Signage</b>	-----	-----	-----	EXIT	-----	-----

\* LOCKDOWN signage is for 432KLD models only. The 432K does not have any signage on the faceplate.



## CERTIFICATIONS

UL 294 Access Control System Units\*

\* Only 432KLD models are UL 294 listed.



## HOW TO ORDER

### FOLLOW STEPS FOR ORDERING

Designates optional step

### 1| SPECIFY MODEL

#### NARROW

**431CN** Alternate Action (AA) On/Off, SPST-NC

**431ON** Alternate Action (AA) On/Off, SPST-NO

**432CN** Momentary (MO), SPST-NC

**432ON** Momentary (MO), SPST-NO

**432KN\*** Momentary (MO) Latching w/ Key Reset, DPST

**434N** Momentary (MO), DPST

**435N** Alternate Action (AA) On/Off, DPST

\* Latching models only available with red mushroom button. Must specify option "R".

#### SINGLE GANG

**431C** Alternate Action (AA) On/Off, SPST-NC

**431O** Alternate Action (AA) On/Off, SPST-NO

**432C** Momentary (MO), SPST-NC

**432O** Momentary (MO), SPST-NO

**432K\*** Momentary (MO) Latching w/ Key Reset, DPST

**432KLD\*** Momentary (MO) Latching w/ Key Reset, DPST

**434** Momentary (MO), DPST

**435** Alternate Action (AA) On/Off, DPST

\* Latching models only available with red mushroom button. Must specify option "R".

#### SIGN

[blank]

[blank]

EXIT

EXIT

[blank]

EXIT

[blank]

#### SIGN

[blank]

[blank]

EXIT

EXIT

[blank]

LOCKDOWN

EXIT

[blank]

### 2| SPECIFY FINISHES

**U** 630 Dull Stainless

**S** 629 Bright Stainless

**C** 605 Bright Brass

**H** 613 Dark Oil Rubbed Bronze

**D** 606 Dull Brass

**Q** 626 Dull Chrome

**P** 625 Bright Chrome

### 3| SPECIFY OPTIONS

**R** Red Button

**L1G** Visual Status Indicator (LED), One Green

**L1R** Visual Status Indicator (LED), One Red

**L2** Visual Status Indicator (LED), One Green & One Red

**LT** Visual Status Indicator (LED), One Tri-Color

**E\*** Add "EXIT" Sign

**B\*\*** No Sign, Blank

\* Available for 431 and 435 models only.

\*\* Available for 432 and 433 models only.

STEP NUMBER:	1	2	3
ORDERING EXAMPLE:	<b>432KLD</b>	<b>U</b>	<b>R</b>



## RELATED PRODUCTS

### RETROFIT BACK BOX

**BB1D** Single Gang, 2 1/4" x 3 3/4" x 2 3/4"



