



C2G
6ft (1.8m) 18AWG Power Cord (IEC320C14 to IEC320C13) - Blue
Part No. CG-17504



When working in a wiring closet or a cabinet space is limited and cords can easily be misidentified and disconnected causing detrimental downtime. Perform maintenance tasks with confidence by using color power cords in a data environment allowing for quick and accurate identification of equipment.

Power Up

Connect PDUs to servers, switches, or other data center equipment. This cable can deliver 15 Amps up to 250 Volts to any connected device ensuring correct operating power

Level Up

Each color power cable is constructed to the highest industry standards, to ensure high-quality installs and deliver the stability and durability that is needed for reliable network performance.

Maintain Excellence

Allow IT technicians to perform maintenance tasks with confidence and easily locate equipment based on functionality or location, saving both time and money using color coded power cables.

Features & Benefits

Full length color jacket with matched color connectors

Constructed of heavy duty 18AWG conductors

Rated up to 250V 10A

UL listed

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120175049	Country Of Origin	China
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Power Cord		

Dimensions

Product Length US	6.0 FT	Cable Length	6 ft
-------------------	--------	--------------	------

Listing Agencies / 3rd Party Agencies

REACH Compliant Yes

Technical Information

Wire Gauge	18 AWG	Jacket Rating	SVT Rated
------------	--------	---------------	-----------

Amperage	10 A	Adapter Rear	C13 IEC
----------	------	--------------	---------

Adapter Front	C14 IEC	Voltage	250 V
---------------	---------	---------	-------
