





THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF **ZONG INTERNATIONAL LTD.** AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF **ZONG INTERNATIONAL LTD.**

RoHS Compliant a


REV.	REVISED DESCRIPTION	DATE	CHECKED
A0	FIRST RELEASE	2019/11/26	



Cable Spec.



Signal Assignment




Remark:

- 100% Open/Short Test
- Conductive Resistance: 10ohms MAX
- Insulation Resistance: 10M ohm MIN.
- HI-POT: DC 300V/10MS.
- The product is Reach/RoHS 2.0 compliant.
- Support 1080P/3D/4K*2K@60Hz
- Bandwidth: 18Gbps

Item NO.	Length
4XHDMI4K2KPRO25	7.63m(25ft)

⑤		HDMI Protective Cap, PE	2PCS	
④	External Mold	Outer Mould 45P PVC, Black	2PCS	
③	Internal Mold	Inner Mould PE	2PCS	
②	Connector	HDMI A PLUG PIN, Gold-Plated	2PCS	
①	Cable	28AWG HDMI2.0 (19+1BC) 96ALB HDMI Cable OD: 7.3mm (0.32BC+FPE)*1P+D+AL] *5C + (0.254BC+HDPE)*4C + AL + D + 96ALB PVCOD: 7.3mm		
ITEM	DESCRIPTIONS & SPECIFICATIONS		QTY	REMARK



TOLERANCES UNLESS OTHERWISE STATED
X. = ± 1
.X = ± 0.2
.XX = ± 0.1

ZONG

ZONG Cable Technology Co., Ltd.
中广视讯线缆技术有限公司

ERP NO.:		SAMPLE DWG NO.:	
DOC No.:		REVISION	A0
CUSTOMER:		UNIT	mm
CUSTOMER P/N:		SCALE	NO
DESCRIPTION	HDMI2.0 19+1BC		PAGE NO 1/1
		DATE	2019/11/26
APPROVAL		CHECKED	
		DRAWN	