

Cisco GLC-T Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m - Cisco Firepower, ASR920, IE2000

**Product ID:** GLCTSTTAA



The GLCTSTTAA is a TAA compliant Cisco GLC-T compatible copper transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1 GbE connectivity over copper cable, for 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 1000 Mbps
- Type: Copper
- Connection Type: RJ45 Connector
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 3,068,049 hours
- Power Consumption: Less than 1.3 Watts
- Digital Diagnostics Monitoring (DDM): No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

## Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

## Features

- **100% CISCO GLC-T COMPATIBLE:** Works with Cisco switches like Firepower, ASR920, IE2000, IE4000, ASR9000 and others
- **TECHNICAL SPECS:** 1000BASE-T 1 Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

---

### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Industry Standards	IEEE 802.3ab 1000BASE-T

---

### Performance

Maximum Data Transfer Rate	1000 Mbps
Max Transfer Distance	100 m (328 ft)
Type	Copper
DDM	No
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	3,068,049 hours
Power Consumption (In Watts)	< 1.3 W

---

### Connector(s)

Local Unit Connectors	RJ-45
-----------------------	-------

---

**Special Notes / Requirements**

Note	For use in 1 Gigabit networking equipment and media converters
------	----------------------------------------------------------------

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	30~75% RH

---

**Physical Characteristics**

Product Length	2.8 in [70.0 mm]
Product Width	0.5 in [13.0 mm]
Product Height	0.5 in [13.5 mm]
Weight of Product	0.8 oz [22.0 g]

---

**Packaging Information**

Package Length	4.8 in [12.1 cm]
Package Width	3.0 in [77.0 mm]
Package Height	1.3 in [33.0 mm]
Shipping (Package) Weight	1.9 oz [55.0 g]

---

**What's in the Box**

Included in Package	SFP transceiver
---------------------	-----------------

---

*\*Product appearance and specifications are subject to change without notice.*

