



Overall length 2.56” (65mm), large ID = 0.59” (15mm), wire end ID = 0.19” (4.8mm)

Material: Insulator Flexible PVC

Ratings: Dielectric Strength 5KV at thinnest cross section

Temperature -20°F (-30°C) to 160°F (71°C)

Color - Black

RoHS 3 compliant

REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± ANGULAR: MACH ± BEND ± TWO PLACE DECIMAL ± THREE PLACE DECIMAL ± INTERPRET GEOMETRIC TOLERANCING PER: MATERIAL CRS FINISH POWDER COAT DO NOT SCALE DRAWING	BLACK BOX®			TITLE: THINNET INSULATOR BOOT		
		NAME	DATE			
	DRAWN	Drawn By	3/11/2013	SIZE B	DWG. NO. FC057	REV A
	ENG APPR.	Approved By	3/11/2013			
	CHECKED	Checked By	3/11/2013			
	COMMENTS:			SCALE: 1:1		
				SHEET 1 OF 1		

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.

©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.