

660

Series

The strongest surface mounted,
multi-purpose locking solution

hes
ASSA ABLOY

Standard Features

- Static strength 1,000 lbs. •
- Dynamic strength over 100 ft-lbs. •
- Endurance over 1,000,000 cycles •
- Available in either 12 or 24 VDC •
- All metal construction •
- Adjustable mounting brackets with final lockdown feature •
- 6 foot cable lead •
- Patented design •
- 3 year limited warranty •

Optional Features

- LBSM - "Locked State" Monitoring •
- Pre-load version •

Electrical

- .24 Amps @ 12VDC continuous duty •
- .12 Amps @ 24VDC continuous duty •
- .70 Amps @ 12VDC (pre-load option) •
- .35 Amps @ 24VDC (pre-load option) •

Accessories

- KO - 660 Key override option •

