

HP LaserJet Envelope Feeder (J8J90A)

Overview

Streamline business mailings with the HP LaserJet Envelope Feeder.



Improve productivity and reduce printer interaction by eliminating the need to manually load envelopes.

Add two HP Envelope Feeders and print up to 150 professional looking envelopes at a time.

Simplifying business mailings by printing envelopes quickly and efficiently with this feeder that holds 75 envelopes.

Specifications

Dimensions (W x D x H)	512 x 558 x 148 mm
Dimensions (W x D x H)	20.15 x 22 x 5.8 in <i>(Without trays and covers; not extended)</i>
Weight	6.8 kg
Weight	15 lb
Package dimensions (W x D x H)	601 x 309 x 620 mm
Package weight	9 kg
UPC number	889894213617
Manufacturer Warranty	90 Day HP Dealer Exchange. Warranty and support options vary by product, country and local legal requirements. Go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 3Y)
What's in the box	HP LaserJet Envelope Feeder; Documentation (Hardware Install Guide)

Additional specifications

Accessory type	Input
Additive metric depth	0
Additive metric height	148
Additive metric width	0
Business filter	cMPS
Cartons per layer	6
Compatibility	HP LaserJet Enterprise MFP M631dn J8J63A, HP LaserJet Enterprise Flow MFP M631h J8J64A, HP LaserJet Enterprise MFP M631z J8J65A, HP LaserJet Enterprise MFP M632h J8J70A, HP LaserJet Enterprise MFP M632fht J8J71A, HP LaserJet Enterprise Flow MFP M632z J8J72A, HP LaserJet Enterprise MFP M633fh J8J76A, HP LaserJet Enterprise Flow MFP M633z J8J78A, HP LaserJet Managed MFP E62555dn J8J66A, HP LaserJet Managed MFP E62565hs J8J73A, HP LaserJet Managed Flow MFP E62565h J8J74A, HP LaserJet Managed Flow MFP E62565z J8J79A, HP LaserJet Managed Flow MFP E62575z J8J80A
Component type	Printer accessories
Count of layers in pallet	3
Electromagnetic compatibility	CISPR 22:2008 (International) - Class A, CISPR 32:2012 (International) - Class A, EN 55032: 2012 (EU) - Class A, EN 61000-3-2: 2014 (EU), EN 61000-3-3: 2013 (EU), EN 55024: 2010 (EU), EMC Directive 2014/30/EU, FCC CFR 47 Part 15 Class A / ICES-003, Issue 6 Class A (US/Canada), Other EMC approvals as required by individual countries
Maximum input capacity (sheets)	Up to 75 envelopes
Media sizes, custom	90 x 148 to 178 x 254 mm
Media sizes, custom	3.5 x 6.3 to 7 x 10 in
Media types	Envelopes, note cards
Metric depth	558
Metric height	148
Metric width	512
Non-Operating Humidity Range	10 to 90% RH
Operating humidity range	10 to 80% RH
Operating temperature range	59 to 90.5°F
Operating temperature range	15 to 32.5°C
Orderable product number	J8J90A
Package dimensions (W x D x H)	23.7 x 12.2 x 24.4 in
Package weight	19.8 lb
Pallet dimensions	40 x 48 x 73.1 in
Pallet dimensions (W x D x H)	1016 x 1220 x 1856 mm

Pallet weight	357.1 lb
Pallet weight	162 kg
Quantity per pallet	18
Safety	IEC 60950-1:2005 +A1:2009 +A2:2013 (International); EN60950-1:2006 +A11:2009 +A1:2010 +A12:2011 +A2:2013 (EU); Low Voltage Directive 2014/35/EU with CE Mark (Europe). Other safety approvals as required by individual countries
Storage temperature range	-22 to 140°F
Storage temperature range	-30 to 60°C
Sub-brand name	LaserJet
Tariff numbers	8443995015 (AM-Base-HTS); 8443999000 (EU-Base-HTS); 84439930 (AP-Base-HTS)
Tray capacity	75
UNSPSC code	44101705
Warranty	90 Day HP dealer Exchange. Warranty and support options vary by product, country and local legal requirements. Go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 3Y)