

## USB 3.1 (10Gbps) Adapter Cable for 2.5"/3.5" SATA Drives - USB-C

**Product ID:** USB31C2SAT3



This USB-C to SATA adapter cable gives you fast and easy access to the data on your 2.5 in./3.5 in. solid-state drives and hard drives. The adapter cable lets you connect your USB-C enabled laptop or desktop computer directly to a SATA drive and access it through ultra-fast USB 3.1 Gen. 2 (up to 10Gbps). It's the ideal accessory for your Dell XPS, MacBook, Chromebook or other USB Type-C enabled device.

The USB-C to SATA adapter cable lets you quickly swap your drives. You can copy or retrieve data from your 2.5 in. or 3.5 in. SATA drive, with no additional accessories required.

The tool-free adapter cable is ideal for IT technicians who need fast access to SATA drives. It's the perfect solution for data migration, drive cloning, and data backup or recovery applications, providing the fast performance of USB 3.1 Gen 2. You can also operate multiple adapters at the same time, when you need simultaneous access to many drives.

USB 3.1 Gen 2 gives you greater bandwidth and speed, with rates of up to 10Gbps - twice the speed of USB 3.0 (also known as USB 3.1 Gen 1). It lets you leverage the high performance of the latest SSDs and hard drives, while alleviating bottlenecks in your data transfers.

The compact, lightweight design of the USB-C to SATA adapter provides easy portability. The adapter features an integrated 1 m cable, so you never have to worry about forgetting to bring your connector cable with you.

You can connect easily to a 2.5 in. solid-state drive or hard drive, using USB power, with no external power required. A universal power adapter is included for use when connecting to your 3.5 in. drives or for any 2.5 in. drives that may require additional power.

The USB31C2SAT3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Certifications, Reports and Compatibility**



## Applications

- Access any SATA 2.5 in. or 3.5 in. SSD/HDD from a USB-C enabled laptop or desktop computer, for easy data migration or drive cloning
- Ideal for technicians who need a quick, easy way to access data on 2.5 in. and 3.5 in. solid-state drives and hard drives
- Back up important data to an external storage device
- Restore your computer from a backup hard drive
- Archive media content such as photos and videos to a bare external drive

## Features

- Connect a 2.5"/3.5" SATA drive to your USB-C enabled laptop or desktop computer, for quick access to your external data
- Fast data transfer rates through USB 3.1 Gen 2 (10Gbps)
- Integrated 1 m cable, for convenient use
- Supports SATA I, II, III (up to 6Gbps)
- Thunderbolt 3 USB-C port compatible
- Tool-free design, for easy drive installation
- TRIM support
- 4Kn support
- Supports drive S.M.A.R.T. data pass through for drive monitoring
- UASP support
- Hot-swap and plug-and-play support
- Power/Activity LED indicator
- Backward compatible with USB 3.0 and USB 2.0 computers

---

### Hardware

Warranty	2 Years
Interface	USB 3.1 Gen 2
Bus Type	USB 3.1 Gen 2

Number of Drives	1
Drive Size	2.5in & 3.5in
Compatible Drive Types	SATA
Drive Installation	Removable
Chipset ID	ASMedia - ASM1351

---

#### Performance

Maximum Data Transfer Rate	10 Gbps
Type and Rate	USB 3.1 Gen 2 - 10 Gbit/s
UASP Support	Yes
TRIM Support	Yes
4Kn Support	Yes
S.M.A.R.T. Support	Yes
Type and Rate	SATA III (6 Gbps)
Hardware Raid Supported	No
Max Drive Capacity	Currently tested with hard drives up to 10TB
Hot Swap Capability	Yes

---

#### Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	USB Type-C (24 pin) USB 3.1 (10Gbps)

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

#### Special Notes / Requirements

Note	Windows 7 and earlier Windows versions do not support TRIM with USB to SATA devices.
------	--

---

#### Indicators

LED Indicators	Power and Activity
----------------	--------------------



---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6 A
Output Voltage	12V DC
Output Current	2.0 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	24

---

**Environmental**

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	0% ~ 80% RH

---

**Physical Characteristics**

Color	Black
Material	Plastic
Cable Length	39.4 in [100 cm]
Product Length	3.4 in [87 mm]
Product Width	1.0 in [25 mm]
Product Height	0.8 in [20 mm]
Weight of Product	2.1 oz [60 g]

---

**Packaging Information**

Package Length	6.7 in [17 cm]
Package Width	5.5 in [14 cm]
Package Height	2.0 in [50 mm]



Shipping (Package) Weight	11.4 oz [324 g]
------------------------------	-----------------

---

**What's in the  
Box**

Included in Package	adapter cable
	universal power adapter (NA/JP, UK, EU, ANZ)
	quick-start guide

---

***\*Product appearance and specifications are subject to change without notice.***

