



Signature Line DDR3L 2GB 1600MHz SODIMM

Patriot's Signature SODIMM modules are the perfect, no hassle upgrade for any notebook. Compatible with Intel's® 4th generation mobile processors and running with just 1.35 low voltage, these SODIMM modules are optimized for ultra low power consumption providing extremely efficient performance.



Patriot's Signature SODIMMS are built from the highest quality, components and hand tested offering consumers rock-solid plug and play performance for the most demanding mobile applications.

Compatible with Windows® 10, Windows® 8, Windows® 7, Windows® Vista, Windows® XP, Windows® 2000, Windows® ME, Linux 2.4 and later, Mac® OS 9, X and later, Patriot's SODIMM modules are backed by a limited lifetime warranty and Patriot's award winning customer support

PRODUCT INFORMATION

PRODUCT NAME:	Signature Line
PATRIOT PART NUMBER:	PSD32G1600L2S
DESCRIPTION:	Patriot Signature DDR3L 2GB PC3-12800 (1600MHz) CL11 SODIMM
CERTIFICATIONS/SAFETY:	RoHS
PRODUCT WARRANTY:	Lifetime Warranty
UNIT UPC:	0814914023365
UNIT WEIGHT:	0.04 lbs / 19 gm
UNIT DIMENSIONS:	0.12" (D) x 2.7" (W) x 1.2" (H) 0.30 cm (D) x 6.9 cm (W) x 3 cm (H)
PACKAGING TYPE:	Blister Pack
PACKAGING WEIGHT:	0.09 lbs / 45 gm
PACKAGING DIMENSIONS:	0.63" (L) x 4.64" (W) x 7.08" (H) 1.6cm (L) x 11.8cm (W) x 18cm (H)
MASTER CARTON WEIGHT:	6.7 Kg
MASTER CARTON DIMENSIONS:	43.5cm x 29cm x 40.5cm
UNITS PER INNER CARTON:	25
UNITS PER MASTER CARTON:	250

FEATURES:

- PC3L-12800 (1600MHz) Data Rate
- 204-Pin Dual in-line memory module
- Non-ECC Unbuffered
- 2 Rank Double-sided module
- 7.8US Refresh Interval (8192 CYCLES/64MS)
- 1.35V Power Requirement
- Auto and self refresh capability
- PCB height: 1181(mil)
- Serial Presence-Detect (SPD)
- 100% Tested
- RoHS Compliant
- JEDEC Compliant
- Works with Intel® 4th Generation mobile processors

For technical support, email us at:
SUPPORT@PATRIOTMEM.COM

MEMORY STORAGE