

Bulk Cat 6 Ethernet Cable - 1000 ft. (304,8m) - Solid - CMR-Rated - Black - TAA Compliant

Product ID: WIR6CMRBK



This bulk Cat6 cable delivers reliable Gigabit network connections, which ensures high-performance capability for your demanding Ethernet applications. The Cat6 cable is riser rated for in-wall installations.

This Category 6 cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

Each of our cables is manufactured using high-quality copper conductors and they are carefully constructed and tested, to keep Near-End Crosstalk (NEXT) well within acceptable limits.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet and 4K or 1080p video streaming, using cables that include 23 AWG copper.

The WIR6CMRBK delivers reliable performance and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Designed for riser installation runs such as in walls, between floors and elevator shafts where CMR fire rating is required
- Deliver data, voice and video over Gigabit networks

Features

- **CAT6 ETHERNET CABLE:** 1000 ft. (304,8m) Solid Cat6 cable is optimized for enterprise 10 Gigabit networks; 550 MHz frequency range enhances throughput capacity; Supports Power over Ethernet (PoE) and 4K or 1080p video streaming
- **QUALITY CONSTRUCTION:** High-quality copper conductors enable a precise fit to minimize wear and signal loss; 23 AWG solid copper supporting a diverse range of Ethernet applications
- **SAFETY AND RELIABILITY:** Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits; Reliable Ethernet connections; Free of noise and EMI/RFI interference
- **APPLICATIONS:** Ideal for riser installations (in-wall, between floor, elevator shafts, etc.) where CMR fire rating is required.; Can be used for network installation at home, office or educational institution
- **SPECIFICATIONS:** CAT6; Black; 1000 foot (304,8 meter); 1000Mbps/10Gbps; 550 MHz; PoE; UTP; 23AWG Pure Bare Copper; CMR Rated (Riser); ETL; TAA

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)

Performance

Maximum Data Transfer Rate	10BASE-T through 1000BASE-T Ethernet
Cable Rating	CAT6 550 MHz

Physical Characteristics

Color	Black
Wire Gauge	23 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Product Width	0.2 in [0.4 cm]
Product Height	0.2 in [0.4 cm]
Weight of Product	28.0 lb [12.7 kg]

**Packaging
Information**

Package Quantity	1
Package Length	18.0 in [45.8 cm]
Package Width	8.9 in [22.7 cm]
Package Height	18.0 in [45.6 cm]
Shipping (Package) Weight	31.3 lb [14.2 kg]

What's in the Box

Included in Package	1 - roll of Cat6 cable
---------------------	------------------------

****Product appearance and specifications are subject to change without notice.***