



C2G
16.4ft (5m) Ultima™ USB 2.0 A/B Cable
Part No. CG-29144



The Ultima USB cable optimizes style, quality, and value in a cable specially designed for high performance. Just plug-and-play for keyboards, mice, modems, printers, and other USB peripherals, and this cable will deliver high speed data transfer up to 480 Mbps. heavy duty 24 AWG power wires provide the proper current to your USB device. Dual foil and braid shielding reduces EMI/RFI interference while twisted pair construction helps reduce crosstalk thus ensuring high speed, error-free data transfer.

The sleek design of the molded connectors makes them easy to grip. The metal connector shield helps to meet FCC requirements on EMI/RFI interference, while a solder-to-connector shell and cable braid create an end-to-end shielding solution for a noise-free connection.

24k gold-plated connectors provide maximum corrosion resistance for error-free data transfer. The charcoal gray cable jacket not only matches your case but disappears behind your desk leaving a clean organized look. Finally, an ultra-flexible jacket makes installation easy.

Features & Benefits

- Plug-and-play design
- Supports transfer rates up to 480 Mbps
- Shielded to prevent unwanted EMI/RFI interference
- Twisted pair construction helps reduce crosstalk

Specifications

General Info

Product Line	C2G	UPC Number	757120291442
Country Of Origin	VietNam	Application Sector	Residential, Commercial
Warranty Type	Lifetime	Type	Cable

Dimensions

Cable Length	16.4 ft
--------------	---------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	USB	Data Transfer Rate	480 Mbps
Adapter Rear	USB-B Male	Adapter Front	USB-A Male
