




C2G
1ft (0.3m) Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Blue
Part No. CG-27140



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120271406	Country Of Origin	VietNam
Application Sector	Residential, Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	1 ft
--------------	------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
-----------------	--------------------------	------------	--------

Cable Type	Snagless, Ethernet Patch Cable, Unshielded (UTP)	Jacket Rating	Standard Non-Rated
Adapter Rear	RJ-45 Male	Adapter Front	RJ-45 Male