

Rackmount KVM Console - Single Port VGA KVM with 19" LCD Monitor for Server Rack - Fully Featured Universal 1U LCD KVM Drawer w/Cables & Hardware - USB Support - 50,000 MTBF

Product ID: RKCONS1901



This rack-mount KVM console provides complete keyboard, monitor and mouse control for a single server or multiple servers, connected through a separate KVM switch (sold separately). The 19 in. console installs into 1U of rack space, offering a space-efficient solution for complete console control.

This KVM console provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in keyboard and a touchpad for intuitive control, as well as an LCD display that supports resolutions up to 1280x1024.

This versatile LCD console has a 19 in. screen. The increased screen space allows you to run multiple applications on the same screen, increasing your productivity.

The rack-mount LCD console slides out from 1U of rack space, enabling you to easily monitor and control a single server or multiple servers when connected through a KVM switch. The rack-mount VGA console features a handle that makes it easy to slide the console in and out of the server rack, keeping your area organized and clutter-free.

The rack console features a single-port KVM module, which enables you to connect it directly to a server. The module offers the flexibility you need to easily integrate it into your existing server infrastructure.

The RKCONS1901 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet

- Manage cabinet-mounted servers and KVM switches

Features

- **FLEXIBLE DESIGN:** This rackmount KVM console drawer works with all KVM switch brands and models that supports VGA and USB interfaces and conveniently slides into the server rack when not in use
- **VERSATILE INTERFACES:** Rack mount monitor w/ 19" Active Matrix TFT 1280 x 1024 LCD 1U height 99 key full keyboard with numeric keypad + Trackpad Supports VGA and USB Integrated Power Supply
- **MAX DURABILITY:** Features durable steel housing design and rails that withstand frequent use, rated to work in environments from 0 to 40 deg. C and a 50,000 hour MTBF
- **TESTED AND PROVEN:** Our KVM consoles are backed by a 2 year warranty with 24/5 by multi-lingual tech support based in North America with free technical support for the life of the product
- **KVM Collection:** Can be purchased with integrated 8-port (RKCONS1908K) or 16-port (RKCONS1916K) KVM or use with StarTech.com enterprise KVM switches: SV831DUSB, SV831DUSBK, SV1631DUSBU, SV1631DUSBK

Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	No
Audio	No
Display Size	19in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Cables Included	Yes

Performance

IP Control	No
------------	----

Maximum Analog Resolutions	1280 x 1024
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1280 x 1024 <i>Lower resolutions are also supported</i>
Contrast Ratio	1000:1
Brightness	250 cd/m
Color Depth	8-bit, 16.7M colors
Pixel Pitch Support	0.264 x 0.264 mm
Maximum Number of Users	1
MTBF	50, 000 Hrs

Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub)
----------------------	----------------------------------

Indicators

LED Indicators	power / status LED
----------------	--------------------

Power

Power Source	International Power Cords
Power Consumption (In Watts)	17W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10 ~ 80% RH

Physical Characteristics

Material	Steel
Product Length	21.0 in [53.3 cm]



Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [43 mm]
Weight of Product	27.0 lb [12.2 kg]
Maximum Mounting Depth	30.7 in [78 cm]
Minimum Mounting Depth	19.7 in [50 cm]

Packaging Information

Package Length	30.1 in [76.5 cm]
Package Width	24.2 in [61.5 cm]
Package Height	7.5 in [19 cm]
Shipping (Package) Weight	35.4 lb [16 kg]

What's in the Box

Included in Package	KVM console
	6 ft [1.8 m] KVM cable
	M5 cage nuts
	M5 screws
	regional power cords (NA, JP, UK, EU, ANZ)
	mounting rails (variable length)
	quick-start guide

****Product appearance and specifications are subject to change without notice.***

