

Rackmount KVM Console - Single Port VGA KVM with 17" LCD Monitor for Server Rack - Fully Featured Universal 1U LCD KVM Drawer w/Cables & Hardware - USB Support - 50,000 MTBF

**Product ID:** RKCONS1701



Providing centralized control of your PC, server, or KVM switch, this single-port rackmount KVM console gives you easy access to your connected system. With a minimal footprint, it mounts in a server rack or cabinet using only 1U of rack space.

The 1U rackmount console features a built-in keyboard, a touchpad for intuitive control, and a 17-inch LCD display that supports resolutions up to 1280x1024.

This single-port KVM console includes everything you need to set up right out of the box:

- 1 VGA KVM Cable
- Mounting Rails
- M5 Cage Nuts and Screws

The rack console features a single-port KVM module, which can be connected directly to a server or PC, or to a KVM switch for access to multiple systems. The KVM module offers the flexibility you need for easily integrating the console into your existing server infrastructure.

Rack consoles provide convenient, rack-mounted control options for single servers or entire server rooms. KVM consoles include LCD display, keyboard, and trackpad, all sliding into 1U of rack space. RKCONS1701 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

## Features

- **FLEXIBLE DESIGN:** This rackmount KVM console drawer works with all KVM switch brands and models that supports VGA and USB interfaces and conveniently slides into the server rack when not in use
- **VERSATILE INTERFACES:** Rack mount monitor w/ 17" Active Matrix TFT 1280 x 1024 LCD 1U height 99 key full keyboard with numeric keypad + Trackpad Supports VGA and USB Integrated Power Supply
- **MAX DURABILITY:** Features durable steel housing design and rails that withstand frequent use, rated to work in environments from 0 to 40 deg. C and a 50,000 hour MTBF
- **TESTED AND PROVEN:** Our KVM consoles are backed by a 2 year warranty with 24/5 by multi-lingual tech support based in North America with free technical support for the life of the product
- **KVM Collection:** Can be purchased with integrated 8-port (RKCONS1708K) or 16-port (RKCONS1716K) KVM or use with StarTech.com enterprise KVM switches: SV831DUSB, SV831DUSBK, SV1631DUSBU, SV1631DUSBK.

---

## Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	No
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Cables Included	Yes

---

**Performance**

IP Control	No
Maximum Analog Resolutions	1280 x 1024
Supported Resolutions	Resolutions up to 1280 x 1024 @ 60Hz
Aspect Ratio	5:4
Response Time	5ms
Contrast Ratio	1000:1
Brightness	250 cd/m
Color Depth	8-bit, 16.7M colors
Pixel Pitch Support	0.264 x 0.264 mm
Viewing Angle	170 (H), 160 (V)
Maximum Number of Users	1
MTBF	50,000 Hrs

---

**Connector(s)**

Host Connectors	VGA (15 pin, High Density D-Sub)
-----------------	----------------------------------

---

**Special Notes / Requirements**

Note	The minimum mounting depth of this rackmount console is less than the length of the console itself. Please consider the length of the rackmount console when evaluating if it will fit into your rack.
------	--

---

**Indicators**

LED Indicators	Power / Status LED
----------------	--------------------

---

**Power**

Power Source	International Power Cords
Input Voltage	100 - 240 AC
Input Current	1.5A
Power Consumption (In Watts)	13W

---



## Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10 ~ 80% RH (non-condensing)

---

## Physical Characteristics

Color	Black
Material	Steel
Cable Length	6ft
Product Length	18.5 in [47.1 cm]
Product Width	17.6 in [44.8 cm]
Product Height	1.7 in [42.5 mm]
Weight of Product	25.9 lb [11.7 kg]
Maximum Mounting Depth	31.1 in [79 cm]
Minimum Mounting Depth	17.7 in [45 cm]

---

## Packaging Information

Package Length	30.1 in [76.5 cm]
Package Width	24.2 in [61.5 cm]
Package Height	7.5 in [19 cm]
Shipping (Package) Weight	37.8 lb [17.1 kg]

---

## What's in the Box

Included in Package	KVM console
	KVM cable
	M5 cage nuts
	M5 screws
	regional power cords (NA, JP, UK, EU, ANZ)

mounting rails

quick-start guide

---

***\*Product appearance and specifications are subject to change without notice.***

