

StarTech.com AOC Breakout Cable for Cisco QSFP-4X10G-AOC10M - 15m/49ft 40G 1x QSFP+ to 4x SFP+ AOC Cable - 40GbE QSFP+ Active Optical Fiber - 40Gbps QSFP Plus/Transceiver Module Breakout Cable - C9300 C3850 (QSFP4X10AO15)

Product ID: QSFP4X10AO15



The SFP4X10AO15 is a Cisco QSFP-4X10G-AOC10M compatible optical quad small form-factor pluggable (QSFP+) breakout cable that is designed, programmed and tested to work with Cisco brand compatible servers or routers and complies with MSA industry standards. Connecting a single QSFP+ port (40 GbE) to four 10G SFP+ ports, this active optical breakout cable is fully hot-pluggable which makes upgrades and replacements seamless by minimizing network disruptions.

The fiber QSFP+ cable is lighter and more flexible than QSFP+ direct-attach cables, making it ideal for installation in tight spaces and over longer distances. It is designed for high-speed interconnects and is great for point-to-point across-rack network switch or server connections, for up to four 10G SFP+ devices.

All StarTech.com QSFP & QSFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP Cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

- Use in 40Gb/10Gb mixed Ethernet network applications
- Point-to-point across-rack server or network switch connections, for up to four devices

Features

- 100% CISCO QSFP-4X10G-AOC10M COMPATIBLE QSFP+ BREAKOUT DAC: Works with Cisco switches like

C9300, C3850, C9300, C9500, C3650 and others

- **TECHNICAL SPECS:** 15m (49ft) Active Optical Cable 40Gbps Active Optical Fiber 1x QSFP+ to 4x SFP+ Pluggable Connector PVC Cable Jacket Hot swappable MSA Compliant
- **DESIGNED FOR SERVER ROOMS:** 40GbE AOC is a convenient alternative to transceivers inside and between racks. Factory termination means high performance & reliability, with less maintenance.
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM warranty and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Low power 40GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers

Hardware

| | |
|-----------------------|--------------------------|
| Warranty | Lifetime |
| Compatible Brand | Cisco |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Type | Active Optical Cable |

Performance

| | |
|------------------------------|------------------------------------|
| Maximum Data Transfer Rate | 40Gbps for QSFP+ / 10Gbps for SFP+ |
| Compatible Networks | 40 Gbps |
| Power Consumption (In Watts) | < 1.5 W (per end) |

Connector(s)

| | |
|-------------|-------|
| Connector A | QSFP+ |
| Connector B | SFP+ |

Environmental

| | |
|-----------------------|----------------------------|
| Operating Temperature | 0C to 70C (32F to 158F) |
| Storage Temperature | -40C to 80C (-40F to 158F) |

Physical Characteristics

| | |
|----------------|------------------|
| Product Length | 49.2 ft [15.0 m] |
| Product Width | 0.5 in [12.0 mm] |



| | |
|-------------------|-------------------|
| Product Height | 0.5 in [12.0 mm] |
| Weight of Product | 11.3 oz [320.0 g] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Length | 12.6 in [32.0 cm] |
| Package Width | 9.6 in [24.5 cm] |
| Package Height | 1.0 in [25.0 mm] |
| Shipping (Package) Weight | 12.2 oz [346.0 g] |

What's in the Box

| | |
|---------------------|------------------------|
| Included in Package | QSFP+ to 4x SFP+ cable |
|---------------------|------------------------|

****Product appearance and specifications are subject to change without notice.***

