



StrongHold™ JP4DW-X20 J-Pro Cable Support, .43", Blk, PA 6.6, Drop Wire, 4",PK10

JP4DW-X20

Panduit JP4DW-X20 J-Hook with Drop Wire and Rod Clip has a patented design, featuring complete horizontal and vertical 1" bend radius control, which prevents pinch points and degradation of cable performance. They are suitable for use in air handling spaces and are UL listed. For use with #12 wire and threaded rod up to 3/8" (9.5mm) in diameter or 1/8" - 7/16" (3.2mm-11.1mm), 4.0" (101.6mm) max. bundle capacity. Made of Nylon 6.6, are black in color, and come in packages of 50.

Specifications

Application	Support J-MOD J-Hooks
Product Type	J-Pro Cable Support
Category 5e Cable Capacity	200
Category 6 Cable Capacity	180
Category 6A Cable Capacity	115
Color	Black
Material	Nylon 6.6
Maximum Flange Thickness (In.)	0.43
Maximum Flange Thickness (mm)	11.1
Maximum J-Hook Bundle Capacity	101.6
Mount Method	Drop Wire
Overall Height (In.)	9.24
Overall Height (mm)	234.7
Overall Length (In.)	6.8
Overall Length (mm)	172.7
Overall Width (In.)	6.8
Overall Width (mm)	172.7
Standards Met	UL, cULus Listed, RoHS Compliant
Sub Brand	StrongHold™
Static Load Capacity (kg)	45.4
Static Load Capacity (lb)	100
Support Type	J-PRO Pre-Assembled J-Hook System

Packaging Detail

UPC	61305602291
Std. Pkg. Qty.	10
Std. Pkg. Volume (cf)	1.2851
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000