



Hi-Speed USB Extension Cable

USB 2.0, Type-A Male to Type-A Female, 480 Mbps, 3 m (10 ft.), Translucent Silver

Part No.: **340496**

EAN-13: 0766623340496 | UPC: 766623340496

Quality connections for superior performance

MANHATTAN Hi-Speed USB 2.0 Extension Cables easily lengthen connections between computers and USB-powered peripherals. Ideal for use with printers, keyboards, external enclosures and an expanding assortment of digital devices, MANHATTAN Hi-Speed USB 2.0 Extension Cables are engineered and constructed of quality materials that support data transfer rates up to 480 Mbps to deliver dependable, error-free transmissions over longer distances. Full foil and braided shielding, gold-plated contacts and molded boots with strain relief help assure maximum conductivity for the fast connection of USB-enabled devices with reduced EMI interference and minimal data degradation.

Features:

- USB Standard-A male to USB Standard-A female
- Extends a USB cable to a maximum of 5 m (16 ft.)
- Speeds of up to 480 Mbps
- Hi-Speed USB for ultra-fast data transfer rates with zero data degradation
- Lifetime Warranty

Specifications:

Standards and Certifications

- UL 2725
- USB 2.0

Connectors

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- (1) USB 2.0 Standard-A male
- (1) USB 2.0 Standard-A female
- Gold plated
- Molded PVC boot

Cable

- 28 AWG conductors
- Shielded
- Withstanding voltage: 300 V DC 10 ms
- Insulation resistance: 5 MOhms
- Contact resistance: 10 Ohms
- Thermal plastic casing

Package Contents

- Hi-Speed USB Extension Cable



