



MMP350-M316 Marker Plate and Tag, 316 SS, Silver, 3.5"x0.75", PK1000

MMP350-M316

The MMP350-M316 Marker Plate provides permanent identification of pipes, valves, cables, and equipment in harsh environments. Designed for use with Panduit Pan-Steel Cable Ties for fast installation at the lowest cost. For on-site marking, use the Metal Indenting Machine (MIM) or Permanent Identification Systems (PES400). 316 Stainless Steel, 3.50"x 0.75"x 0.010" (88.9 mm x 19.1 mm x 0.3 mm). 1000 pieces per box.

Specifications

Product Type	Marker Plate and Tag
Color	Silver
Environment	Indoor/Outdoor
For Use With	MLT-S, MIM, PES197, PES400
Material	316 Stainless Steel
Maximum Characters per Line	18
Maximum Lines of Text	3
Overall Length (In.)	3.5
Overall Length (mm)	88.9
Standards Met	RoHS Compliant
Overall Thickness (In.)	0.01
Overall Thickness (mm)	0.3
Overall Width (In.)	0.75
Overall Width (mm)	19.1
Label Application	Cable & Wire Marking
Part Features	Deliver maximum visibility for medium to high volum applications that are exposed to dirt and paint.

Packaging Detail

UPC	07498308982
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0578
Std. Ctn. Qty.	4000
Std. Ctn. Volume (cf)	0.2314