

BEST SELLER



Super-Grip® SGABM30-AV-C300 Super-Grip™ Mount, Black, High Heat/UV PA6.6, VHB

SGABM30-AV-C300

The Panduit SGABM30-AV-C300 super grip acrylic-based adhesive backed cable tie mount is applied with very high-bond adhesive. They are made of heat stabilized and weather resistant Nylon 6.6 and are for use with miniature, intermediate, and standard cross-section cable ties. Designed for outdoor use, especially in harsh and high-temperature environments. They measure 1.12" x 1.12" (28.6mm x 28.6mm), supplied in strips of 2, are black in color and come in packages of 100.

Specifications

Application	Low Profile Super-Grip™ Adhesive Backed Cable Tie Mounts, Used Where Space is Limited, to Keep Bundle Close to Mounting Surface and with Super-Grip™ Cable Ties
Product Type	Cable Tie Mount
Color	Black
Environment	Indoor/Outdoor
Material	Heat Stabilized Weather Resistant Nylon 6.6
Maximum Operating Temperature (°C)	93
Maximum Operating Temperature (°F)	200
Minimum Operating Temperature (°C)	-35
Minimum Operating Temperature (°F)	-31
Mount Method	VHB Adhesive Tape
Overall Height (In.)	0.33
Overall Height (mm)	8.4
Overall Length (In.)	1.12
Overall Length (mm)	28.5
Overall Width (In.)	1.12
Overall Width (mm)	50.3
Resistance Properties	Heat and UV Resistant
Standards Met	CE Compliant, RoHS Compliant
Static Load Capacity (kg)	0.567
Static Load Capacity (lb)	1.25
Sub Brand	Super-Grip®
For Use With	Super-Grip Miniature, Intermediate, Standard Cross-Section Ties

Packaging Detail

UPC	07498319572
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0540
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.2701