

PMAX-1501



Cable Gland for Outdoor Domes (except Hemispheric Domes)

► Specifications

Device

Product Type	Camera Mount
Application Environment	Outdoor
Description	Cable Gland for Outdoor Domes (except Hemispheric Domes)

General

Thread Size	PF 3/4"
Supported Cable Diameter Range	4.3-6.4mm
Weight	18.5g (0.42lb)
Dimensions	(Ø x L): 48mm x 33mm (1.89" x 1.30")
Color	Black
Material	Nylon 66
Warranty	1 Year(s)



► Related Products

Dome - Dome

E73A		5MP Outdoor Dome with D/N, Adaptive IR, Basic WDR, Fixed lens, f2.93mm/F2.0 (HOV:82.3°), H.264, 1080p/30fps, DNR, Audio, MicroSDHC/MicroSDXC, PoE, IP67, IK10, DI/DO
E83A		5MP Outdoor Dome with D/N, Adaptive IR, Basic WDR, Vari-focal lens, f2.8-12mm/F1.4 (HOV:69.2°-28.2°), H.264, 1080p/30fps, DNR, Audio, MicroSDHC/MicroSDXC, PoE, IP67, IK10, DI/DO
E84A		2MP Outdoor Dome with D/N, Adaptive IR, Basic WDR, SLLS, Vari-focal lens, f2.8-12mm/F1.4 (HOV:92.5°-35.9°), H.264, 1080p/30fps, DNR, Audio, MicroSDHC/MicroSDXC, PoE, IP67, IK10, DI/DO

Dome - Zoom Dome

B81		5MP Outdoor Zoom Dome with D/N, Adaptive IR, Basic WDR, 3x Zoom lens, f3-9mm/F1.2-2.1 (HOV:85.7°-30.5°), DC iris, Auto Focus, H.264, 1080p/30fps, DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, IP67, IK10, DI/DO
B83		2MP Video Analytics Outdoor Zoom Dome with D/N, Adaptive IR, Extreme WDR, SLLS, 3x Zoom lens, f3-9mm/F1.3-2.2 (HOV:102.1°-36°), DC iris, Auto Focus, H.264, 1080p/60fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, IP67, IK10, DI/DO, Built-in Analytics
B85		2MP Outdoor Zoom Dome with D/N, Adaptive IR, Basic WDR, SLLS, 3x Zoom lens, 3-9mm/F1.2-2.1 (HOV:103.6°-36.2°), DC iris, Auto Focus, H.264, 1080p/30fps, DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, IP67, IK10, DI/DO
E815		5MP Outdoor Zoom Dome with D/N, Adaptive IR, Basic WDR, 4.3x Zoom lens, f3.1-13.3mm/F1.4-4.0 (HOV:64.74°-25.8°), P-Iris, Auto Focus (for installation), H.264, 1080p/30fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE, IP67, IK10, DI/DO
E816		10MP Outdoor Zoom Dome with D/N, Adaptive IR, Basic WDR, 4.3x Zoom lens, f3.1-13.3mm/F1.4-4.0 (HOV:90.6°-34.3°), P-Iris, Auto Focus (for installation), H.264, 1080p/30fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE, IP67, IK10, DI/DO

PTZ - Mini PTZ

B911		3MP Video Analytics Outdoor Mini PTZ with D/N, Extreme WDR, SLLS, 10x Zoom lens, f4.7-47mm/F1.6-3.0 (HOV:58°-5.8°), DC iris, Auto Focus, H.265/H.264, 1080p/60fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, IP67, IK10, DI/DO, Built-in Analytics
B912		5MP Video Analytics Outdoor Mini PTZ with D/N, Extreme WDR, SLLS, 10x Zoom lens, f4.7-47mm/F1.6-3.0 (HOV:50.67°-5.14°), DC iris, Auto Focus, H.265/H.264, 1080p/30fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, IP67, IK10, DI/DO, Built-in Analytics