



C-USB/C

USB 2.0 Type-C Cable



Kramer's C-USB/C cables connect USB-C enabled devices with standard USB-A, B and Micro B devices (laptops, hard drives, legacy printers, hubs, smartphones, tablets and cameras). C-USB/C cables offer a whole new level of connectivity to devices using the new USB Type-C connector. The symmetrical, low profile USB Type-C connector can be plugged in any direction, eliminating the frustration of getting the port insertion just right

FEATURES

Quality Construction - High-quality shielded twisted pair (STP) construction, helps to prevent electromagnetic interference and ensures reliable data communication

Reversible USB Type-C Connector

Max. Data Rate - 480Mbps

Current Rating - 3A and 5A

PC, Mac & Mobile Compatible

Plug and Play - For printers, scanners, keyboards and other digital devices

Backward Compatibility - USB specifications 1.0 and 1.1

Molded Strain Relief - On the USB A, B & Micro B ends

RoHS Compliant



TECHNICAL SPECIFICATIONS

ELECTRICAL	TYPE: USB 2.0
	MAX. DATA RATE: 480Mbps
	POWER RATING: 100W max
PHYSICAL	CONNECTOR A: USB Type-C male
	CONNECTOR B: C-USB/CC – USB Type-C male
	C-USB/CB – USB Type-B male
	C-USB/CA – USB Type-A male
	C-USB/CMicroB – USB Type-Micro B male
	CONNECTOR PLATING: Nickel
	CONDUCTORS: 28AWG
	CABLE SHIELD TYPE: Aluminum-Mylar foil with braid
STANDARDS COMPLIANCE	OVERALL SHEATH DIAMETER: 4.0mm
	OUTER SHEATH COLOR: White
	REGULATORY: RoHS 2011/65/EU



CONFIGURATIONS

C-USB/CC-6	USB 2.0 USB-C(M) to USB-C(M)
C-USB/CC-10	USB 2.0 USB-C(M) to USB-C(M)
C-USB/CB-6	USB 2.0 USB-C(M) to USB-B(M)
C-USB/CB-10	USB 2.0 USB-C(M) to USB-B(M)
C-USB/CA-6	USB 2.0 USB-C(M) to USB-A(M)
C-USB/CA-10	USB 2.0 USB-C(M) to USB-A(M)
C-USB/CMicroB-3	USB 2.0 USB-C(M) to USB Micro-B(M)
C-USB/CMicroB-6	USB 2.0 USB-C(M) to USB Micro-B(M)