



PUM-100-M0 Cable Tie Mount

PUM-100-M0

The fir tree push mount is black and requires a panel hole diameter of 0.35 to 0.40" (9.0 to 10.0 mm). It is made of weather-resistant nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness. It comes in packages of 1000.

Specifications

Application	They Are a Reliable and Cost Effective Solution for Securing Wire Harnesses in The Automotive, Marine, White Goods, Heavy Equipment and Mass Transit-Rail Markets
Product Type	Cable Tie Mount
Color	Black
Environment	Indoor/Outdoor
Material	Nylon 6.6
Maximum Compatible Panel Thickness (In.)	0.275
Maximum Compatible Panel Thickness (mm)	7
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Mount Method	Fir Tree Mount
Overall Height (In.)	0.66
Overall Height (mm)	16.9
Overall Length (In.)	0.64
Overall Length (mm)	16.2
Overall Width (In.)	0.64
Overall Width (mm)	16.2
Resistance Properties	UV-Resistant
Standards Met	RoHS Compliant
For Use With	Miniature, Intermediate, Standard Cross-Section Ties

Packaging Detail

UPC	07498339821
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.1410
Std. Ctn. Qty.	5000
Std. Ctn. Volume (cf)	0.7051