



SLK-79-FSR-M

DATE	CHANGES	INTL	REV
01.19.16	Original	AH	1.0



KEY SWITCH

MATERIAL: Industrial Silicone Rubber
 LIFE: Greater Than 10 Million Cycles
 TRAVEL: 0.055 in.
 ACTUATION FORCE: 4.76 oz. +/- 1.06oz (135g +/- 30g)
 FEEDBACK: Tactile with Mechanical Snap

TEMPERATURE RANGE

STORAGE: -40°F to +158°F (-40°C to +70°C)
 OPERATING: -4°F to +140°F (-20°C to +60°C)

VIBRATION

POWER SPECTRAL DENSITY: .04g²/HZ
 FREQUENCY RANGE: 20Hz-2Khz
 DURATION OF TEST PER AXIS: 3 hours

POWER

PS2:
 KEYBOARD: 200mA@5V (from Keyboard port)
 POINTER: 35mA@5V (from Mouse port)
 USB: 235mA@5V (from CPU port)

HUMIDITY

100% Humidity Resistant

SHOCK

3 X 11 ms pulses of 50g on each of 3 axis

WEIGHT

1.00 lbs +/- 0.10 lbs (0.45 kg +/- 0.05 kg)

PROPRIETARY AND CONFIDENTIAL



iKey, Ltd.
 2621 Ridgpoint Dr. Suite 235
 Austin, Texas 78754

©2016 iKey, Ltd.
 Voice: (512) 837-0283
 Fax: (512) 927-8530

Part Number: SLK-79-FSR-M

Drawing Title: SLK-79-FSR-M-MKT

Drawing Number: MKT0381

Revision: 1.0


Sheet: 1 OF 2

Date: 01.19.16

ALH

SLK-79-FSR-M MOUNTING

DATE	CHANGES	INTL	REV
01.19.16	Original	AL	1.0



PROPRIETARY AND CONFIDENTIAL



iKey, Ltd.
2621 Ridgpoint Dr. Suite 235
Austin, Texas 78754

©2016 iKey, Ltd.
Voice: (512) 837-0283
Fax: (512) 927-8530

Part Number: SLK-79-FSR-M

Drawing Title: SLK-79-FSR-M-MKT

Drawing Number: MKT0381

Revision: 1.0

Sheet: 2 OF 2

Date: 01.19.16

ALH