ProductSheet
HP LaserJet Managed Flow MFP E62665h (3GY16A)

This HP LaserJet MFP with JetIntelligence combines performance, energy efficiency, and security.[1]

This HP LaserJet MFP with JetIntelligence combines exceptional performance and energy efficiency with professional-quality documents right when you need them—all while protecting your network from attacks with the industry's deepest security.[1]



The world's most secure printing[1]
With HP Sure Start, each printer regularly checks its operating code and repairs itself from attempted hacks.

High-speed performance meets energy efficiency
Speed through tasks and save paper. Print two-sided documents nearly as fast as single-sided.

Pages, Performance, and Protection.
Produce sharp text, bold blacks, and crisp graphics with precision black toner.

Featuring

Consumable Access Control

Data logger & Print Engine Failure Sensor

Fixed-size Cassette Guides

LLC Life Optimization

HP Sure Start

Run-time Intrusion detection

Specifications

Print Resolution Technologies	FastRes 1200; 1200 x 1200 dpi
Print quality black (best)	Up to 1200 x 1200 dpi
Print speed black (ISO, A4)	Up to 61 ppm
Print speed black (ISO, letter)	Up to 65 ppm
Print speed	Print speed up to 65 ppm (black)
Functions	Print, Copy, Scan and Optional Fax
Duplex printing	Automatic (standard)
Duty cycle (monthly, A4)	Up to 450,000 pages
Duty cycle (monthly, letter)	Up to 450,000 pages[7]
Printer smart software features	Print preview, duplex printing, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, easy-access USB
Copier smart software features	Auto scale; Reduce/enlarge from scanner glass (25 to 400 percent); Collate; Auto color detection; Two-sided copying; Image adjustments (darkness, background cleanup, sharpness); Job build
Scanner advanced features	Optimize text/picture; Image adjustments; Job build; Output quality setting; Selectable scan resolution 75 to 600 dpi; Auto detect color; Edge Erase; Job notification; Blank page suppression; HP Quick Sets; HP EveryPage; Auto orientation; Embedded Optical Character Recognition (OCR), Auto crop to page; Auto-tone
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology; Instant-on Copy
Replacement cartridges	HP Black Managed LaserJet Toner (50,000 yield) W9004MC. This printer uses newer generation HP cartridges identifiable by a “P” at the end of the cartridge lot number. More at www.hp.com/go/learnaboutsupplies[5]
Supplies feature	HP JetIntelligence Cartridge
Connectivity, standard	1 Hi-Speed Device USB 2.0; 2 Hi-Speed USB 2.0 Host; 1 Gigabit Ethernet; 1 Hardware Integration Pocket
Connectivity, optional	HP Jetdirect 2900nw Print Server J8031A; HP Jetdirect 3000w NFC/Wireless Accessory J8030A; HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A
Network capabilities	Yes, via HP Jetdirect Ethernet embedded print server (standard) which supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); 802.11a/b/g/n wireless networking (optional).
Wireless capability	Optional, enabled with purchase of a wireless hardware accessory. Single band Wireless Station and Wi-Fi Direct functionality available with HP Jetdirect 3000w NFC/Wireless Accessory J8030A, Dual band Wireless Station and Wi-Fi Direct functionality available with HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A, Dual band Wireless Station functionality available with HP Jetdirect 2900nw Print Server J8031A
Mobile printing capability	Apple AirPrint™; Google Cloud Print™; HP ePrint; Mopria™ Certified; Roam capable for easy printing
Network protocols, supported	Via built-in networking solution: TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, IPP 2.0, Apple AirPrint™, HP ePrint, FTP Print, Google Cloud Print; DISCOVERY: SLP, Bonjour, Web Services Discovery; IP CONFIG: IPv4 (BootP, DHCP, AutoIP, Manual, TFTP Config, ARP-Ping), IPv6 (Stateless Link-Local and via Router, Stateful via DHCPv6); Management: SNMPv2/v3, HTTP/HTTPs, Telnet, TFTP Config, FTP FW Download, Syslog; Security: SNMPv3, SSL Cert Management, Firewall, ACL, 802.1x
Software included	No software solutions are included in the Box, only on http://hp.com, http://123.hp.com
Compatible Operating Systems	Windows Client OS (32/64 bit), Win10, Win8.1, Win 8 Basic, Win8 Pro, Win8 Enterprise, Win8 Enterprise N, Win7 Starter Edition SP1, UPD Win7 Ultimate, Mobile OS, iOS, Android, Mac, Apple® macOS Sierra v10.12, Apple® macOS High Sierra v10.13, Apple® macOS Mojave v10.14, Discrete PCL6 Printer Driver, For more information on the supported operating systems go to http://support.hp.com, Enter your product name and search, Click on User Guides and enter your product name and search for User Guide, Search for your (Product Name) User Guide, Search for the Supported Operating Systems section, UPD PCL6 / PS Printer Drivers, Supported Operating systems, For more information on the supported operating systems see www.hp.com/go/upd
Sustainable impact specifications	Mercury free
Energy star certified	Yes
Ecolabels	ENERGY STAR® qualified; EPEAT® Silver; CECP[1]
Blue Angel compliant	Yes, Blue Angel DE-UZ 219—only ensured when using Original HP supplies
Copy speed (black, normal quality, A4)	Up to 61 cpm
Copy speed black (normal, letter)	Up to 65 cpm
Copy speed black duplex (A4)	Up to 50 cpm
Copy speed black duplex (Letter)	Up to 53 cpm

Digital sending standard features	Scan to E-mail; Scan-to-Sharepoint; Save-to-Network Folder; Save-to-USB drive; Send to Sharepoint; Send to FTP; Send to Internet Fax; Local Address Book; SMTP over SSL; Blank Page Removal; Edge Erase; Auto Color Sense; Auto Crop To Content; Compact PDF; Auto Tonescale; Auto Orientation; Multi-Pick Detect; Auto Straighten; Auto Crop To Page; OCR
Digital sending optional features	Authentication; Data transfer; Digital fax (send to LAN, Internet); Local Address Book; Metadata capture and validation; OCR; Scan workflow management; Send-to-folder; Send-to-printer; Send-to-workflow; via HP Embedded Capture; Optional via HP Digital Sending Software (HP DSS)
Faxing	No
Scan speed (normal, A4)	Up to 83 ppm/167 ipm (b&w), up to 83 ppm/167 ipm (color)
Scan speed (normal, letter)	Up to 90 ppm/180 ipm (b&w), up to 90 ppm/180 ipm (color)
Scan file format	Digital Send: PDF, Hi-Compression PDF, JPEG, TIFF, MTIFF, XPS, PDF/A, TEXT (OCR), Unicode TEXT (OCR), RTF (OCR), Searchable PDF (OCR), Searchable PDF/A (OCR), HTML (OCR), CSV (OCR); Scan to easy access USB: PDF, JPEG, TIFF, MTIFF, XPS, PDF/A, TEXT (OCR), Unicode TEXT (OCR), RTF (OCR), Searchable PDF (OCR), Searchable PDF/A (OCR), HTML (OCR), CSV (OCR); Print from easy access USB: PDF, PS, Print Ready files (.prn, .pcl, .cht)
Scan input modes	Front panel applications: Copy; E-mail; Save to Network Folder; Save to USB; Save to Device Memory; Save to SharePoint; Open Extensibility Platform (OXP) applications, HP Scan or user application via TWAIN
Scan technology	Charge Coupled Device (CCD); Contact Image Sensor (CIS)
Scanner type	Flatbed, ADF
Display area (imperial)	6.37 x 4.78 in
Display area (metric)	16.2 x 12.1 cm
Display	8.0-in (20.3 cm) Color Graphics Display (CGD) with touchscreen; rotating (adjustable angle) display; illuminated Home button (for quick return to the Home menu)
Minimum dimensions (W x D x H)	512 x 558 x 640 mm
Minimum dimensions (W x D x H)	20.15 x 22 x 25.2 in
Weight	33.73 kg[3] *(With print cartridges)*
Weight	74.35 lb *(With print cartridges)*
Power consumption	740 watts (printing/copying), 29.0 watts (ready), 3.3 watts (sleep), < 0.1 watts (Auto Off/Manual On), < 0.1 watts (Manual Off)[4]
Power supply type	Built-in 115V or 220V Power Supply
What's in the box	HP LaserJet Managed Flow E62665h MFP; HP Original LaserJet Toner Cartridge (~11,000 pages); Documentation (Hardware Install Guide); Power cord; Fixed-Size Cassette Guides[2]
Manufacturer Warranty	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements. Go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 4G)

Top Recommended Displays, Accessories and Services

Smart Cards and SmartCard Readers	
HP HIP2 Keystroke Reader	Y7C05A
HP USB Universal Card Reader	X3D03A
DDR3 Memory	
HP 1 GB x32 144-pin (800 MHz)DDR3 SODIMM	E5K48A
HP 2 GB x32 144-pin (800 MHz) DDR3 SODIMM	E5K49A
HP 2GB 144-Pin DDR3 TAA Version DIMM	2NR09A
Input Trays	
HP LaserJet 1x550 Paper Feeder and Cabinet	J8J91A
HP LaserJet 1x550-sheet and 2000-sheet HCI Feeder and Stand	J8J92A
HP LaserJet 3x550-sheet Paper Feeder with Cabinet	J8J93A
HP LaserJet 550-sheet Feeder Tray	J8J89A
Envelope Feeders	
HP LaserJet Envelope Feeder	J8J90A
Fax Upgrades	
HP MFP Analog Fax Accessory 700	2EH31A
Printer Cables	
HP Foreign Interface Harness	B5L31A
Port Cables and Cable Adapters	
HP Internal USB Ports	B5L28A
Printer Accessibility Accessories	
HP Accessibility Kit	2TD64A
External Print Servers	
HP Jetdirect 3100w BLE/NFC/Wireless Accessory	3JN69A
Internal Print Servers	
HP Jetdirect LAN Accessory	8FP31A
EIO Hard Drives	
HP High-Performance Secure Hard Disk	B5L29A
HP Laser Printer Supply Kits	
HP 300 ADF Roller Replacement Kit	J8J95A
HP LaserJet 110V Maintenance Kit	J8J87A
Printing SW Solution Licenses	
HP HID Mobile Access Mifare DES Fire Keystroking Reader	35H11A
HP SIM for HID iClass for HIP2 Reader	Y7C07A
Imaging and Printing Hardware Support Onsite Svc	
HP 3 year Next Business Day w/DMR Service for Color LaserJet E625xx E626xx Managed	U9NM8E
HP 3 year 4 hour 9x5 w/DMR Service for Color LaserJet E625xx E626xx Managed	U9NN1E
Imaging and Printing Commercial Care Pack Services	
HP Installation Service with network configuration for Workgroup Printer(1 unit)	U9JT2E

Messaging Footnotes

[1] Based on HP review of 2018 published security features of competitive in-class printers. Only HP offers a combination of security features that can monitor to detect and automatically stop an attack then self-validate software integrity in a reboot. For a list of printers, visit http://www.hp.com/go/PrintersThatProtect. For more information: http://www.hp.com/go/printersecurityclaims

Technical Specifications Footnotes

[1] EPEAT® registered where applicable. EPEAT registration varies by country. See http://www.epeat.net for registration status by country.

[2] Standard cartridges included; yields 11,000 black pages. Average black declared yields based on ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see http://www.hp.com/go/learnaboutsupplies.

[3] With print cartridges

[4] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115 V device.

[5] Average black declared yields based on ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see http://www.hp.com/go/learnaboutsupplies.

[7] Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups.

Learn more at
hp.com

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.