

USB-C to VGA and HDMI Adapter - 2-in-1 - 4K 30Hz - Space Grey

Product ID: CDP2HDVGA



This USB-C to VGA and HDMI adapter offers a portable solution for connecting your USB Type-C laptop to a VGA or HDMI display. The multiport video adapter also works as a splitter, enabling you to simultaneously output an identical video signal to two separate monitors (1 x HDMI and 1 x VGA).

Avoid the hassle of carrying different adapters, with a 2-in-1 USB-C monitor adapter. With VGA, and HDMI outputs, you can conveniently connect your laptop to any HDMI or VGA-equipped display, using this multiport adapter.

The adapter features a durable aluminum enclosure and can withstand being carried in your travel bag.

The HDMI output on this USB-C video adapter supports UHD resolutions up to 4K 30Hz, while the VGA output supports HD resolutions up to 1920 x 1200.

The USB-C video adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

CDP2HDVGA is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect to virtually any VGA or HDMI display while traveling
- Use as a video splitter to output an identical image to a VGA and HDMI monitor simultaneously splitting the image
- Output video to a secondary VGA, or HDMI monitor

Features

- Maximize your laptop's video compatibility with a 2-in-1 adapter: USB-C to HDMI and VGA
- Support resource-demanding applications with UHD resolutions up to 4K 30Hz
- Space Gray adapter matches your Space Gray MacBook or MacBook Pro

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	HDMI - 1.4
	VGA
Chipset ID	ITE - IT6222

Performance

Video Revision	HDMI 2.0
Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920 x 1200 @ 60Hz (VGA)
Maximum Digital Resolutions	3840 x 2160 @ 30Hz (HDMI)
Supported Resolutions	Maximum HDMI output: 3840 x 2160 @ 30Hz
	Maximum VGA output: 1920 x 1200 @ 60Hz
	<i>Lower resolutions and refresh rates may also be supported</i>
Audio Specifications	HDMI - 7.1 Channel Audio
MTBF	1,576,016 hours

Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
-------------	-------------------------------------



Connector B	VGA (15 pin, High Density D-Sub)
	HDMI (19 pin)

Special Notes / Requirements

Note	HDMI and VGA can output video at the same time. If both video outputs are connected, they'll display the same image at a maximum resolution of 1920x1200 @ 60Hz
	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	5~90% RH

Physical Characteristics

Color	Space Gray
Accent Color	Black
Material	Aluminum
Cable Length	6.0 in [15.2 cm]
Product Length	8.1 in [20.5 cm]
Product Width	2.4 in [62.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Length	7.0 in [17.9 cm]
Package Width	3.1 in [80.0 mm]
Package Height	0.8 in [20.0 mm]
Shipping (Package) Weight	2.2 oz [62.0 g]



**What's in the
Box**

Included in Package Travel A/V Adapter

****Product appearance and specifications are subject to change without notice.***

