




ELECTRICAL RATINGS

Parameter	Rating
Input Voltage	120 VAC, 50/60Hz
Input Power (max)	253W
Output Power	225W
Relay Lock Outputs	16 @ 2.5A Class 2 Power Limited
Auxiliary Outputs	16 @ 2.5A Class 2 Power Limited
Maximum Charge Current	FPO75: 1A, 40AH maximum FPO150: 2A, 80AH maximum
Low Power Disconnect	at 70% of battery voltage
Systems BTU/Hr	99 BTU/Hr
Operating Temperature	32 to 122F (0 to +50C)
Efficiency	86% 120VAC 60Hz In, Full Load
Agency Approvals	UL294, UL603, UL1076, ULC S318, ULC S319, CSA C22.2 #205, FCC Part 15, SubpartB, CSFM IEC 62368-1:2014, EN 55032:2015, EN6100-3-2:2014, EN6100-3-3:2013, EN55024:2010+A1:2015,BIS IS13252(Part1):2010, REACH 209, ROHS 3

OVERVIEW

Mercury Unified Power Systems combine FlexPower power modules alongside access control hardware in one compact and secure UL listed solution. Unified Power features include:

- **Built in Fire Alarm disconnect** unlocks doors on a fire alarm.
- **Low battery cutoff** protects batteries from deep discharge.
- **Dedicated fast charger** prolongs battery life
- **Enhanced surge immunity** for input/output protection
- **Locksafe™** optimized voltages provide longterm lock protection
- **OutSmart™** Visual LED notification (12V/Green, 24V/Blue)
- **Network ready** with optional Netlink™ module
 - Monitor power supply and battery in NetLink dashboard
 - Remote test batteries
- **Lifetime Warranty** LifeSafety Power's quality commitment

SYSTEM DETAILS

- **1 x FPO75, 1 x FPO150** 225W Total Output, 120 VAC Input, AC Fault and System Fault form C contacts may be triggered by low/no battery, short to earth ground, power supply failure, or blown fuse
- **2 x C8P (16 Relay Lock Outputs)** 2.5A Class 2 power limited outputs, programmable for failsafe/failsecure, FAI, NC/NO input, voltage or dry output per zone. Dual buss voltage selection by zone, OutSmart dual color LEDs
- **2 x D8P (16 Auxiliary Outputs)** 2.5A Class 2 Power Limited Outputs, dual buss voltage selection by zone, OutSmart dual color LEDs
- **E6M1 Enclosure** Size: 30.0H x 23.0W x 6.5D in (30.0 x 23.0 x 6.5 cm)
 - **Enclosure E6**
 - **Backplate E6M1**
- **System Weight** 49.95 lbs (22.66kg)

ORDERING

FPO75/150-2C8P2D8PE6M1

120 VAC, 225W

AGENCY LISTINGS

US | Canada | Mexico | Europe | UK | India | Australia | New Zealand | RoHS



LifeSafety Power

10027 S. 51st Street, Suite 102

Phoenix, AZ 85044 USA

(888) 577-2898

info1@lifesafetypower.com

Disclaimer:

This datasheet was generated programatically by LifeSafety Power's Online Product Generator on 07/03/2024. Because of this, it may be possible that the model depicted is not possible for LifeSafety Power to build. It is the responsibility of the viewer of this datasheet to confirm that the model depicted is within the limitations of the product line. Contact LifeSafety Power for confirmation of fitment or compatibility. Specifications subject to change without notice.