



Signature Line DDR4 4GB 2666MHz (PC4-21300) UDIMM

Patriot's Signature Line DDR4 Non-ECC unbuffered memory delivers the quality, reliability and performance expected for today's mainstream computer needs. This 4GB is designed to run at PC4-21300 (2666MHz) at CAS 19 latency timings for better overall system responsiveness when using demanding application. Built using the highest quality components and hand tested, Patriot ensures every module meets and exceeds industry standards to offer you a hassle-free plug-and-play memory upgrade. With free customer service and a lifetime warranty, Patriot's Signature Line DDR4 memory modules are the perfect option for any PC system build or upgrade for faster performance.



PRODUCT INFORMATION

PRODUCT NAME:	Signature Line
PATRIOT PART NUMBER:	PSD44G266641
DESCRIPTION:	Patriot Signature DDR4 4GB (1x4GB) 2666MHz (PC4-21300) CL19 UDIMM
CERTIFICATIONS/SAFETY:	RoHS
PRODUCT WARRANTY:	Lifetime Warranty
UNIT UPC:	0814914024287
UNIT WEIGHT:	0.04 lbs / 22 gm
UNIT DIMENSIONS:	0.11" (D) x 5.24" (W) x 1.22" (H) 2.8mm (D) x 133mm (W) x 31mm (H)
PACKAGING TYPE:	Blister Pack
PACKAGING WEIGHT:	0.06 lbs / 30.5 gm
PACKAGING DIMENSIONS:	0.63" (D) x 4.64" (W) X 7.08" (H) 16mm (D) x 118mm (W) x 180mm (H)
MASTER CARTON WEIGHT:	18.7lb/8.5 Kgs
MASTER CARTON DIMENSIONS:	17.13"(D) x 11.42"(W) x 15.94" (H) 435mm (D) x 290mm (W) x 405mm (H)
UNITS PER INNER CARTON:	25
UNITS PER MASTER CARTON:	250

FEATURES:

- Series: Signature Line
- Form Factor: 288-Pin Unbuffered Dual In-Line Memory Module (UDIMM)
- Technology : DDR 4 Non-ECC Unbuffered
- 100% Tested
- RoHS Compliant
- Limited lifetime warranty

SPECIFICATIONS:

- Capacity: 4GB (1x4GB)
- Frequency: 2666MHz (PC4-21300)
- Timings: 19-19-19-43
- (One) 1 Rank single sided module
- Voltage: 1.2V

For technical support, email us at:
SUPPORT@PATRIOTMEM.COM

MEMORY STORAGE

