



VA-102P12

10-Output 12V DC Power Supply

| DC Power Out



The VA-102P12 is a 10-output power supply that powers 12V DC powered devices. The VA-101P12 can supply a maximum of 1A of current to each of ten devices for a total of 10A. The power supply is especially useful in high-population installations for saving space and eliminating a large number of 12V DC power adapters. The MD model is suitable for medical applications

FEATURES

Space Saving - Replaces up to 10 individual 12V DC power supplies for Kramer TOOLS™, Kramer PicoTOOLS™, and Kramer 12V DC Desktop models

Outputs - 10 12V DC outputs that supply 1A max. current for each output for a total of 10A total

Indicator - Power LED



TECHNICAL SPECIFICATIONS

OUTPUTS:	10 12V DC @1A max. current per output
INDICATOR:	Power ON LED
POWER CONSUMPTION:	100-240V AC, 2.0A
OPERATING TEMPERATURE:	0° to +40°C (32° to 104°F)
STORAGE TEMPERATURE:	-40° to +70°C (-40° to 158°F)
HUMIDITY:	10% to 90%, RHL non-condensing
INCLUDED ACCESSORIES:	10 DC to DC cables, 95cm (3.1ft) per cable; AC power cord
Product Dimensions	21.46cm x 16.30cm x 4.36cm (8.45" x 6.42" x 1.72") W, D, H
Product Weight	1.2kg (2.6lbs) approx
Shipping Dimensions	35.10cm x 21.20cm x 7.20cm (13.82" x 8.35" x 2.83") W, D, H
Shipping Weight	1.7kg (3.7lbs) approx

