

Eaton MBP10A

Catalog Number: MBP10A

Eaton HotSwap Maintenance Bypass 10A. C14 Input, 4 x C13 outlet

General specifications

Product Name	Catalog Number
Eaton HotSwap MBP Maintenance Bypass PDU	MBP10A
	Product Length/Depth
	188 mm
Product Height	Product Width
44 mm	483 mm
Product Weight	Certifications
3.8 kg	Contact Manufacturer



Product specifications

Resources

Auto shutdown function

No

Number of Outputs C13

4

Electric current - max

10A

Construction type

482.6 mm (19 inch) device

Color

Black

Transfer time

8 ms

Form factor

Rack

Potential free switch contact

No

Output voltage range

192-264 V

Standard factory warranty

1 Year

Output frequency

50-60 Hz

Phase (input)

Single-phase

Input connection

C14

Output nominal voltage

230V default (220/230/240V)

Feed type

1

Input nominal voltage

230V default (220/230/240V)

Used with

5P, 5PX, 5SX, 9PX

Input voltage range

192-264 V

Input frequency range

50Hz-60Hz

Type of Accessory

Bypass

Nominal frequency

50-60 Hz

Communication

None

Altitude

0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)

Phase (output)

Single-phase



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia