



REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	11/13/2019

MARKING: BLACK BOX CORPORATION --- CATEGORY 6 SHIELDED --- E196163-E (UL) C
 (UL) CM SSTP 75°C 4PR 26AWG ANSI/TIA-568.2-D & ISO/IEC 11801 ED.2 &
 EN 50288-5-2 & IEC 60332-1-2 PATCH CABLE



EVNSL0272YY-XXFT
 CABLE LENGTH: 01,02,03,05,06,07,10,15,20,25,30(FT)
 CABLE COLOR: BK,BL,GN,GY,OR,RD,WH,YL....



Conductor	Bare Copper 26AWG 7/0.0060inch approx
Insulation	Thickness:MIN at any point:0.0079inch MAX AVG:0.0138inch Diameter:0.0421inch approx
Jacketing PVC	Thickness:MIN at any point:0.0197inch MAX AVG:0.0217inch Diameter:0.2402inch approx

WIRE	CAT.6 SSTP Stranded 26AWGX4P
PLUG	Molding Molded 8P8C 50u"(1.27 μm) Gold 3 piece plug

RJ45 Plugs Standard - IEC 60603-7

L	T(INCHES)
0~9.9FT	+3IN/-0
10FT~99.9FT	+6IN/-0
100FT+	+12IN/-0

WIRE CONNECTION			
WIRE COLOR	P1	PAIRS	P2
WHITE/ORANGE	1	=====	1
ORANGE	2	=====	2
WHITE/GREEN	3	=====	3
BLUE	4	=====	4
WHITE/BLUE	5	=====	5
GREEN	6	=====	6
WHITE/BROWN	7	=====	7
BROWN	8	=====	8
DRAIN	SHELL	=====	SHELL

NOTES:
 1. CABLE ASS'Y MUST PASS CONTINUITY TEST.Fluke Channel Test.

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.
 ©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 FRACTIONAL ±
 ANGULAR: MACH ± BEND ±
 TWO PLACE DECIMAL ±
 THREE PLACE DECIMAL ±
 INTERPRET GEOMETRIC TOLERANCING PER:
 MATERIAL: CRS
 FINISH: POWDER COAT
 DO NOT SCALE DRAWING

BLACK BOX NETWORK SERVICES

NAME: CYK	DATE: 11/13/2019	TITLE: Category 6 Molded Shielded XXXX patch cable
ENC APPR: BOBO	11/13/2019	SIZE: B
CHECKED: CP	11/13/2019	DWG. NO: EVNSL0272YY-XXFT
COMMENTS:		REV: A
		SCALE: 1:1
		SHEET 1 OF 1