

## OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

### Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: 11712VH

**Model Number:** JBN242-102D20ST5

**Category:** Basic

**Sub Category:** Standard

**Power Configuration:** 20A, 120V, 1.9kW

**Physical Configuration:** 66in / 1683mm, Vertical

**Product Summary:** rPDU, Basic Standard, 20A, 120V, 1.9kW, Vertical, (24) NEMA 5-20R, 10ft power cord with 5-20P, Black Powder Coat.

### Plug Form:



5-20P

### Receptacle:



NEMA 5-20R  
(Quantity: 24)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

Quantity Of Inputs	1
Voltage	100-120V
Current	20A
VA per Input (Load Capacity)	1.9kW (120V)
Frequency	50/60Hz

<b>Over Current Protection</b>	None
<b>Switch</b>	No
<b>Power Cable Wire Gauge</b>	12/3
<b>Power Cable Length</b>	10ft
<b>Plug Type</b>	NEMA 5-20P
<b>Receptacle/Socket Type #1</b>	NEMA 5-20R
<b>- Quantity on Face</b>	24
<b>- Style</b>	Duplex
<b>- Maximum Output per Receptacle/Socket</b>	20A
<b>- Voltage per Receptacle/Socket</b>	120V
<b>Continuous Operating Temperature Range</b>	10-45C / 50-113F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	66in / 1683mm Vertical Rackmount
<b>7938 Vertical Mounting Bracket Kit</b>	Yes
<b>Toolless Mounting Hardware - Center to Center Spacing</b>	61.25in and 64.75in
<b>Country of Origin</b>	USA, TAA Compliant and Buy American Act COTS Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 60950
<b>Chassis Dimensions (LxWxD)</b>	66.25in x 2.0in x 2.0in
<b>Shipped Weight</b>	13lbs (5.9kg)