


LG 32" FHD Infrared Touch Screen Solution



Infrared Interactive Solution

The TSi touch solution is Infrared based, allowing for a high accuracy interactive experience. The usage of Infrared technology allows for virtually any input to be detected (pen/stylus, user's fingers, palms, gloved fingers). The TSi touch solution is a cold rolled steel chassis integrated with tempered cover glass, which increases durability and optical clarity, while protecting the display.



Multi-Touch Screen
 True multi-touch support for all major operating systems. 10 simultaneous touch points are available.



Easy Integration
 Unrivaled simplicity makes installation easier and faster



Ultra-Fast Response Time
 Allows for split second reactions between touch point and screen



HID Compliant
 Maximum compatibility with numerous operating systems, plug-and-play



Superior Design
 Cold rolled steel chassis combined with tempered glass provides additional protection to the LCD panel



Customizable
 Custom colors and silk screening available

Specifications

Display Models	32SE3KE-B, 32SM5KE-B
Touch Screen (Display Not Included)	TSI32NL10TACCZZ
32SE3KE-B Integrated Touch Screen (Display Included)	TSI32PLTUTACCZZ
32SM5KE-B Integrated Touch Screen (Display Included)	TSI32PLTBTACCZZ
Protective Glass	1/8" Clear Tempered Cover Glass
Structure Material	Black Powder Coated Cold Rolled Steel
Touch Technology	IR
Touch Points	10
Response Time	6 - 16ms
Touch Accuracy	+/- 2mm (Over 99% Area)
Interface	Type A USB/M
Communication	USB 2.0
Receiver Extender	N/A
Touch Power Source	USB
Width/Height/Depth Including Monitor	30.04" x 18.15" x 2.95"
Touch Screen Weight	17.64 lbs
Display Integrated Weight	32.80 lbs
Boxed Dimensions	31.50" x 20.00" x 5.00"
OS Support	Windows, Google Chrome, Android, Mac, Linux