


55" NEC Projected Capacitive Touch Screen Solution



Projected Capacitive Touch Solution

TSItouch's line of projected capacitive touch displays are engineered specifically for consumer and commercial customers who are looking for a rugged and durable touch screen without having to sacrifice on image quality. Featuring a seamless flat front bezel design, the monitor can easily be wiped clean, thereby eliminating having to worry about dust and dirt collection, which helps extend the use of your display and enhances your touch experience.



Multi-Touch Screen
 True multi-touch support with up to 100 simultaneous touch points for all major operating systems



Easy Integration
 Unrivaled simplicity makes installation easier and faster



Ultra-Fast Response Time
 Allows for split second reactions between touch point and screen



HID Compliant
 Maximum compatibility with numerous operating systems, plug-and-play



Superior Design
 Zero bezel flat front, clear tempered touch screen with excellent optical performance



Easy to Clean
 Water and dust resistant

Specifications

| | |
|--|---|
| Display Models | V554Q |
| Touch Screen (Display Not Included) | TSI55NNTAPGJGZZ |
| V554Q Integrated Touch Screen (Display Included) | TSI55PNTAPGJGZZ |
| Protective Glass | 1/8" Anti-Glare Cover Glass |
| Structure Material | Black Powder Coated Cold Rolled Steel |
| Touch Technology | PCAP |
| Touch Points | 40 |
| Response Time | 6 - 16ms |
| Touch Accuracy | +/- 2mm (Over 99% Area) |
| Interface | Type A USB/M |
| Communication | USB 2.0 |
| Remote Control Receiver | N/A |
| Receiver Extender | N/A |
| Touch Power Source | USB |
| Width/Height/Depth Including Monitor | 50.28" x 29.45" x 3.07" |
| Touch Screen Weight | 39.9 lbs |
| Display Integrated Weight | 98.99 lbs |
| Boxed Dimensions | 53.50" x 33.00" x 7.50" |
| OS Support | Windows, Google Chrome, Android, Mac, Linux |