

4K Interactive Displays for Collaborative Meeting Rooms




IFP-Series

Meetboard. 

Simplify Your Meeting Room

Built on the Android OS platform; Meetboard® are designed to get meetings and presentations going right away, without the need for projectors, whiteboards, PCs or installing additional software. Eliminate cable clutter and enjoy a clean and organized meeting room thanks to wireless mirroring options. Present, brainstorm and take notes without cables in between or markers that are running out of ink.





Quickly
Start Meeting

Enjoy Clear Image
Presentation

Save and Share
Files Instantly

The New Generation of Meetings

AG Neovo's IFP-Series, Meetboard, is the all-around interactive display that streamlines the meetings process. Since meetings can't wait for slow loading screens, Meetboard's on-board whiteboard app and launcher allows participants to directly access materials and get the meeting going without delay. Meeting materials and presentations are bright and crisp on the 4K display, ensuring that content is clear and compelling. And files and notes relevant to the meeting can be shared with ease, through QR code, email, or cloud drives.




Loaded with Built-in Interactive Apps

Draw and brainstorm with the Meetboard app, make a compelling presentation with WPS Office, or wirelessly share content from your PC, Mac or mobile device with the screen-sharing app. Meetboard comes with all the apps needed for collaborating and sharing ideas out of the box.




Meetboard App

User-friendly interactive whiteboard software designed for interactive meetings and group discussions.



Writing & Drawing

Participants can draw and insert images for demonstrating ideas.



Dual Pens

Two styluses for simultaneous annotation with two colours.



Easy Share

Instantly share meeting files via email, QR code and cloud drives.





Connecting People and Devices has Never Been Easier

Collaborating on projects requires not only the input of your team, but also their devices and content. That is why Meetboard supports 802.11ac Wi-Fi and Bluetooth. A powerful screen-sharing app makes those connections extremely usable; It enables device mirroring and remote controlling from individual devices, no matter what operating systems your team members use: Windows 11, macOS, Android, or iOS.

Made for Hands-On Collaboration

Engaging with ideas over an electronic display can often present hurdles to participation. Meetboard lowers those hurdles with multi-touch and natural writing capabilities. Multiple participants, using their fingers or styluses, can simultaneously draw and annotate on Meetboard as intuitive as using a whiteboard.

Another common obstacle is not having the right driver for your content, an obstacle Meetboard does away with. Its Plug-and-Play Windows support allows Windows users to activate applications like PowerPoint and OneNote directly on the display—all without additional drivers.



Assistive Menu Lets Your Team Focus on What Matters

Meetings shouldn't stop for technical issues. Enter Meetboard's dedicated assistive menu, which works on any input source and Android apps, giving participants the power to access certain functions and shortcuts, like adjusting audio/brightness, capturing screenshots, toggling between tasks, and taking down notes.

Meet Your Team Remotely Everywhere

AG Neovo brings an FMC-06 floor mounting cart to life to fulfil the needs of on-site and virtual collaborations in the changing world. You can quickly install Meetboard on FMC-06 without additional effort and bring all the accessories together; meanwhile, ensure the display remains secure with lockable castors. With excellent mobility and user-friendly design, Meetboard brings the collaborative meeting to the next level out of your imagination.



Features

- 4K UHD 3840 x 2160 resolution
- IPS Panel technology offers high colour accuracy and wide viewing angles
- Incorporates IR touch technology
- ScreenShare Pro App for multi-display sharing
- Instant meeting files sharing via email, QR code and built-in cloud drives
- 20-point simultaneous multi-touch capability
- Windows 11 ready - plug and play support for Windows 7/8/10/11
- User-friendly whiteboard application for collaborative meetings
- Two styluses for simultaneous annotation with two colours
- View, edit & create – office documents with WPS Office Suite App
- Android OS 8.0
- Built-in USB 3.0 for faster transfer speeds with storage devices
- Built-in speakers and audio mini-jack in/out connection
- Wall mount and Wi-Fi module are included for quick installation

Specifications

IFP-6502

IFP-7502

Panel

Panel Type	LED-Backlit TFT LCD (IPS Technology)	LED-Backlit TFT LCD (IPS Technology)
Panel Size	64.5	74.5
Max. Resolution	UHD 3840 x 2160	UHD 3840 x 2160
Pixel Pitch	0.372 mm	0.430 mm
Brightness	350 cd/m²	350 cd/m²
Contrast Ratio	1200:1	1100:1
Viewing Angle (H/V)	178°/178°	178°/178°
Display Colour	1.07B	1.07B
Response Time	5 ms	5 ms
Surface Treatment	Anti-Glare Treatment (Haze 25%), 3H Hard Coating	Anti-Glare Treatment (Haze 28%), 2H Hard Coating

Frequency

Frequency (H)	30 kHz-80 kHz	30 kHz-80 kHz
Frequency (V)	50 Hz-76 Hz	50 Hz-76 Hz

Signal Input

HDMI	2.0 x 3	2.0 x 3
VGA	15-Pin D-Sub x 1	15-Pin D-Sub x 1

Signal Output

HDMI	2.0 x 1	2.0 x 1
------	---------	---------

External Control

RS232 In	9-Pin D-Sub	9-Pin D-Sub
LAN	RJ45 x 1	RJ45 x 1

Embedded Player

OS	Android 8.0	Android 8.0
CPU	Dual core A73+Dual core A53	Dual core A73+Dual core A53
Memory	3 GB	3 GB
Storage	16 GB	16 GB

Other Connectivity

USB	2.0 x 3 / 3.0 x 3	2.0 x 3 / 3.0 x 3
-----	-------------------	-------------------

Audio

Audio In	Stereo Audio Jack (3.5 mm)	Stereo Audio Jack (3.5 mm)
Audio Out	Stereo Audio Jack (3.5 mm), S/PDIF	Stereo Audio Jack (3.5 mm), S/PDIF
Internal Speakers	16W x 2	16W x 2

Touch Screen

Panel Interface	USB 2.0 x 2 (Type-B)	USB 2.0 x 2 (Type-B)
Technology	Infrared Touch Frame	Infrared Touch Frame
Positional Accuracy	±1.5 mm	±1.5 mm
Single Touch Plug & Play	Windows 2000/XP/Vista/CE 6.0, macOS	Windows 2000/XP/Vista/CE 6.0, macOS
Multi-touch Plug & Play	Windows 7/8/10/11, Android/Linux (kernel version 3.5+), Chrome OS (39 or above)	Windows 7/8/10/11, Android/Linux (kernel version 3.5+), Chrome OS (39 or above)
Multi-touch Support by Driver	macOS (supported by UPDD driver)	macOS (supported by UPDD driver)

Power

Power Supply	Internal	Internal
Power Requirements	AC 100-240V, 50/60 Hz	AC 100-240V, 50/60 Hz
On Mode	155W	165W
Standby Mode	< 0.5W	< 0.5W
Off Mode	< 0.3W	< 0.3W

Glass

Thickness	4.0 mm (0.16")	4.0 mm (0.16")
Reflection Rate	< 10%	< 10%
Transmission Rate	≥ 88%	≥ 88%
Hardness	≥ 8H	≥ 8H
Gloss	75±5 GU	75±5 GU

Operating Conditions

Temperature	0°C-40°C (32°F-104°F)	0°C-40°C (32°F-104°F)
Humidity	10%-90% (non-condensing)	10%-90% (non-condensing)

Storage Conditions

Temperature	-20°C-60°C (-4°F-140°F)	-20°C-60°C (-4°F-140°F)
Humidity	10%-90% (non-condensing)	10%-90% (non-condensing)

Mounting

VESA FPMPI	Yes (600 x 400 mm)	Yes (800 x 400 mm)
------------	--------------------	--------------------

Dimensions

Product w/o Base (W x H x D)	1489.0 x 897.0 x 86.0 mm (58.6" x 35.3" x 3.4")	1710.0 x 1020.0 x 86.0 mm (67.3" x 40.2" x 3.4")
Packaging (W x H x D)	1656.0 x 1050.0 x 204.0 mm (65.2" x 41.3" x 8.0")	1860.0 x 1140.0 x 280.0 mm (73.2" x 44.9" x 11.0")

Weight

Product w/o Base	39.0 kg (86.0 lb)	50.6 kg (111.6 lb)
Packaging	55.7 kg (122.8 lb)	72.9 kg (160.7 lb)

Regulation Approval

Certifications & Compliance	CE, LVD, FCC, WEEE, REACH, RoHS, BSMI	CE, LVD, FCC, WEEE, REACH, RoHS, BSMI
-----------------------------	---------------------------------------	---------------------------------------

Accessories

Supplied	Power Cord, HDMI Cable, USB Cable, Remote Control, Batteries, Quick Start Guide, Touch Pen, Wall Mount, Wi-Fi / Bluetooth Module	Power Cord, HDMI Cable, USB Cable, Remote Control, Batteries, Quick Start Guide, Touch Pen, Wall Mount, Wi-Fi / Bluetooth Module
----------	--	--

Optional Accessories

Floor Mount (Landscape only)	FMC-03+LMK-04, FMC-04+LMK-04, FMC-06	FMC-03+LMK-04, FMC-04+LMK-04, FMC-06
Ceiling Mount (Landscape only)	CMP-01+LMK-01	-
Wall Mount (Landscape only)	LMK-01, LMK-03	LMK-03
Stand	STD-08	-

Specifications

IFP-8602

Panel

Panel Type	LED-Backlit TFT LCD (IPS Technology)
Panel Size	85.6"
Max. Resolution	UHD 3840 x 2160
Pixel Pitch	0.494 mm
Brightness	350 cd/m²
Contrast Ratio	1200:1
Viewing Angle (H/V)	178°/178°
Display Colour	1.07B
Response Time	5 ms
Surface Treatment	Anti-Glare treatment (Haze 28%), 2H Hard coating

Frequency

Frequency (H)	30 kHz-80 kHz
Frequency (V)	50 Hz-76 Hz

Signal Input

HDMI	2.0 x 3
VGA	15-Pin D-Sub x 1

Signal Output

HDMI	2.0 x 1
------	---------

External Control

RS232 In	9-Pin D-Sub
LAN	RJ45 x 1

Embedded Player

OS	Android 8.0
CPU	Dual core A73+Dual core A53
Memory	3 GB
Storage	16 GB

Other Connectivity

USB	2.0 x 3 / 3.0 x 3
-----	-------------------

Audio

Audio In	Stereo Audio Jack (3.5 mm)
Audio Out	Stereo Audio Jack (3.5 mm), S/PDIF
Internal Speakers	16W x 2

Touch Screen

Panel Interface	USB 2.0 x 2 (Type-B)
Technology	Infrared Touch Frame
Positional Accuracy	±1.5 mm
Single Touch Plug & Play	Windows 2000/XP/Vista/CE 6.0, macOS
Multi-touch Plug & Play	Windows 7/8/10/11, Android/Linux (kernel version 3.5+), Chrome OS (39 or above)
Multi-touch Support by Driver	macOS (supported by UPDD driver)

Power

Power Supply	Internal
Power Requirements	AC 100-240V, 50/60 Hz
On Mode	294W
Standby Mode	< 0.5W
Off Mode	< 0.3W

Glass

Thickness	4.0 mm (0.16")
Reflection Rate	< 10%
Transmission Rate	≥ 88%
Hardness	≥ 8H
Gloss	75±5 GU

Operating Conditions

Temperature	0°C-40°C (32°F-104°F)
Humidity	10%-90% (non-condensing)

Storage Conditions

Temperature	-20°C-60°C (-4°F-140°F)
Humidity	10%-90%(non-condensing)

Mounting

VESA FPM/PMI	Yes (800 x 600 mm)
--------------	--------------------

Dimensions

Product w/o Base (W x H x D)	1957.2 x 1160.0 x 86.0 mm (77.1" x 45.6" x 3.4")
Packaging (W x H x D)	2211.0 x 1370.0 x 280.0 mm (87.1" x 53.9" x 11.0")

Weight

Product w/o Base	66.0kg (145.5 lb)
Packaging	98.8kg (217.8 lb)

Regulation Approval

Certifications & Compliance	CE, LVD, FCC, WEEE, REACH, RoHS
-----------------------------	---------------------------------

Accessories

Supplied	Power Cord, HDMI Cable, USB Cable, Remote Control, Batteries, Quick Start Guide, Touch Pen, Wall Mount, Wi-Fi / Bluetooth Module
----------	--

Optional Accessories

Floor Mount (Landscape only)	FMC-03+LMK-04, FMC-04+LMK-04, FMC-06
------------------------------	--------------------------------------