

DS-PR1-60




- Detection angle: 100°
- Detection range: 60m
- Line crossing(Max. 4 trigger lines) and Zone alarm(Max. 8 Zones)
- 2 Selectable frequency band
- Coverage up to 3,000 sq m
- Up to 32 detection targets
- Links up to 4 speed domes for auto target-tracking and the speed domes can be mounted separately
- Function of radar-speed dome linkage: smooth stream*, mandatory switch of speed dome tracking target , parking action and field of view display for each speed dome
- Supports 3 low-voltage relays, 1 high-voltage relay
- Multiple radars can link to one speed dome
- movable trigger line(whole line or one endpoint), editable trigger line length, and configurable trigger line direction
- Selectable applications including open mode, shrub mode, and custom mode (with adjustable sensitivity)
- 3 selectable Scenario Modes optional
- Up to 4 targets can be tracked by 4 speed domes respectively
- Water resistant and vandal proof (IP67 and IK09)Multiple anomaly detections: Anti-masking
- Supports standard PoE and 12 VDC



▪ Specification

Detection performance	
Detection Range	60m
Detection Angle	100°
Velocity range	- 8.7 to 8.7 m/s
Radar transmit power	≤20 dBm
Microwave Frequency	24.05 ~ 24.25GHz
Max. Target number	32
Range measurement accuracy	± 0.75m
Velocity measurement accuracy	± 0.1m/s
Date Fresh rate	10 frames / s
Features	
Zones	8
Exception detection	Communication failure alarm, Movement alarm, Anti-masking detection alarm
Tamper-Proof	Tampering alarm
Schedule	Auto Arm/Disarm Schedule
Firmware undate tools	Web / iVMS-4200
Configuration tools	Web / iVMS-4200
Protocol	HTTP, DNS, NTP, TCP, UDP, DHCP, ARP, SSH
Interface	
Alarm output	4 Relay Outputs(NO/NC)
Relay output	3-ch: 0.5A/125VAC, breakdown voltage: 1kV 1-ch: 10A/240VAC. Breakdown voltage: 2.5kV
Netowrk interface	1 RJ45 10M/100M self-adaptive, PoE
Power interface	802.3at standard PoE or 12VDC
Serial port	RS232
Indicator	Dual-color LED
RF Transmission	
RF Modulation	FMCW
Electrical characteristics	
Power supply	Standard PoE / 12VDC
Power Consumption	6W
General	
Operation temperature	-40°C to 65°C
Operation humidity	10% to 90%
Shell material	PC+ABS
Dimension(WxHxD)	206 mm × 228 mm × 61 mm (8.11" × 8.98" × 2.40")
IP Rate	IP67
IK Rate	IK09
Anti-corrosion	NEMA 4X
Weight	1.84 kg (4.06 lb)
Application scenario	Outdoor
Color	White
Installation height	1.2 - 4m (Recommend Height: 2.5m)
Installation method	Multiple installations with different brackets
Bracket	Multiple brackets

▪ Dimension



▪ Accessory

▪ Included

DS-PRB-1310	DS-PRB-1200	DS-PRB-1120	DS-PRB-2200	DS-PRB-1110
Radar bracket	Radar bracket	Radar bracket		Radar bracket
				

▪ Available Model

DS-PR1-60



Distributed by



HIKVISION®

Headquarters

No.555 Qianmo Road, Binjiang District,
Hangzhou 310051, China
T +86-571-8807-5998
overseasbusiness@hikvision.com

Hikvision USA
T +1-909-895-0400
sales.usa@hikvision.com

Hikvision Australia
T +61-2-8599-4233
salesau@hikvision.com

Hikvision India
T +91-22-28469900
sales@pramahikvision.com

Hikvision Canada
T +1-866-200-6690
sales.canada@hikvision.com

Hikvision Thailand
T +662-275-9949
sales.thailand@hikvision.com

Hikvision Europe
T +31-23-5542770
sales.eu@hikvision.com

Hikvision Italy
T +39-0438-6902
info.it@hikvision.com

Hikvision Brazil
T +55 11 3318-0050
Latam.support@hikvision.com

Hikvision Turkey
T +90 (216)521 7070- 7074
sales.tr@hikvision.com

Hikvision Malaysia
T +601-7652-2413
sales.my@hikvision.com

Hikvision UK & Ireland
T +01628-902140
sales.uk@hikvision.com

Hikvision South Africa
Tel: +27 (10) 0351172
sale.africa@hikvision.com

Hikvision France
T +33(0)1-85-330-450
info.fr@hikvision.com

Hikvision Kazakhstan
T +7-727-9730667
nikia.panfilov@hikvision.ru

Hikvision Vietnam
T +84-974270888
sales.vt@hikvision.com

Hikvision UAE
T +971-4-4432090
salesme@hikvision.com

Hikvision Singapore
T +65-6684-4718
sg@hikvision.com

Hikvision Spain
T +34-91-737-16-55
info.es@hikvision.com

Hikvision Tashkent
T +99-87-1238-9438
uzb@hikvision.ru

Hikvision Hong Kong
T +852-2151-1761
info.hk@hikvision.com

Hikvision Russia
T +7-495-669-67-99
saleru@hikvision.com

Hikvision Korea
T +82-[0]31-731-8817
sales.korea@hikvision.com

Hikvision Poland
T +48-22-460-01-50
info.pl@hikvision.com

Hikvision Indonesia
T +62-21-2933759
Sales.Indonesia@hikvision.com

Hikvision Colombia
sales.colombia@hikvision.com