



HP DeskJet Plus 4155 All-in-One Printer

Simple multitasking

All the features. All the value. Print, scan, copy, 24 months send mobile fax with HP Smart App, and get a 35-page automatic feeder and worry-free wireless.¹ Count on simple setup with HP Smart App.²



Dynamic security enabled printer. Intended to be used with cartridges using only HP original electronic circuitry. Cartridges with modified or non-HP electronic circuitry may not work, and those that work today may not work in the future.
<http://www.hp.com/go/learnaboutsupplies>

ISO Speed: Black: Up to 8.5 ppm; Color: Up to 5.5 ppm
Print Resolution: Black (best): Up to 1200 x 1200 rendered dpi; Color (best): Up to 4800 x 1200 optimized dpi color (when printing from a computer on selected HP photo papers and 1200 input dpi)
Scan Resolution: Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi
Copy Resolution: Black (text & graphics): Up to 300 x 300 dpi; Color (text & graphics): Up to 300 x 300 dpi
Standard Connectivity: 1 Hi-Speed USB 2.0
Mobile Printing Capability: HP Smart app; Apple AirPrint™
Duty cycle: Monthly (letter): Up to 1000 pages
Display: Icon LCD display
Paper Handling: 60-sheet input tray; 25-sheet output tray

Added extras so you can do more

- Work fast and hands-free—the 35-page auto-feeder helps you complete scan and copy jobs quickly.
- Easily handle tasks and get a lot from one device – print, scan, and copy.
- Easily print, scan, and copy everyday documents from your smartphone, using HP Smart app.²
- Save time by sending a mobile fax from your smartphone, tablet, or PC for 24 months, with HP Smart app.²

Simple setup. Simple printing.

- Get started fast with simple setup that guides you through each step, using HP Smart app.²
- Get better range and faster, more reliable connections using dual-band Wi-Fi® with self-reset.¹
- Get connected with Bluetooth® and start printing fast from your smartphone or tablet – easy setup.⁴
- Get connected and start printing. Easily connect your printer to your computer with the built-in USB port.⁶

Save up to 50% on ink and never run out^{3,4}

- With HP Instant Ink, ink is automatically ordered and delivered to your door, and you pay a lot less.^{3,4}
- With HP Instant Ink, you can enroll in a plan that enables you to print up to 15 pages per month for free.⁹
- Original HP ink cartridges deliver sharp text and vibrant graphics for all your everyday documents and photos.



¹ Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at hp.com/go/mobileprinting. Wi-Fi is a registered trademark of Wi-Fi Alliance®. Supports both 5.0 GHz and 2.4 GHz using up to 12 non-overlapping channels vs only 3 non-overlapping channels for 2.4 GHz only. Supports 5.0 GHz band (up to 150 mbps) vs 2.4 GHz band (up to 72.2 mbps). Internet access required and must be purchased separately. ² Requires the HP Smart app download. For details on local printing requirements see <http://hp.com/go/mobileprinting>. Certain features/software are available in English language only. Internet access required and must be purchased separately. Fax capabilities are for sending a fax only, and may require additional purchase. For more information, see <http://hpsmart.com/mobile-fax>. ³ Compared to majority of OEM mobile printing apps for inkjet & laser printers & all-in-ones for home & home office, priced less than or equal to \$429.99 USD. Market share as reported by IDC CYQ2 2018 Hardcopy Peripherals Tracker. Claim based on lab testing and research of printer manufacturer's mobile print apps and Keypoint Intelligence - Buyers Lab study commissioned by HP. See Sept 2018 report at <http://www.keypointintelligence.com/HPSmartApp>. ⁴ Mobile device needs to support Bluetooth v4.2+ and be enabled. A mobile app such as HP ePrint or HP Smart must be installed and opened for printing. Mobile device must be within 5 feet of the printer. For details, see <http://www.hp.com/go/bleprinting>. Bluetooth is a trademark owned by its proprietor and used by HP under license. ⁵ Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at <http://hp.com/go/mobileprinting>. Wi-Fi is a registered trademark of Wi-Fi Alliance®. ⁶ USB cable not included; purchase separately. ⁷ Compared with standard-fill Original HP ink cartridges. High-yield ink cartridges not included; purchase separately. For more information, see <http://hp.com/go/learnaboutsupplies>.

HP DeskJet Plus 4155 All-in-One Printer Technical specifications

Functions / Multitasking supported	Print, copy, scan, wireless, send mobile fax / No
Print speed ⁵	Black (ISO): Up to 8.5 ppm; Color (ISO): Up to 5.5 ppm; First page out black: As fast as 15 sec; First Page Out Color: As fast as 19 sec
Print resolution	Black (best): Up to 1200 x 1200 rendered dpi; Color (best): Up to 4800 x 1200 optimized dpi color (when printing from a computer on selected HP photo papers and 1200 input dpi)
Print technology	HP Thermal Inkjet
Print cartridges number	2 (1 each black, tri-color)
Borderless printing	No
Standard print languages	HP PCL 3 GUI; HP PCLm (HP Apps/UPD); URF (AirPrint)
Scan type / Technology	Flatbed, ADF Contact Image Sensor (CIS)
Scan resolution	Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi
Scan file format	JPEG, TIFF, PDF, BMP, PNG
Scan input modes	Front-panel scan
Scan size maximum	Flatbed: 8.5 x 11.69 in
Scan speed	N/A
Bit depth / Grayscale levels	24-bit/256
Digital sending standard features	No
Copy speed ³	Black (ISO): Up to 6 cpm; Color (ISO): Up to 3 cpm
Copy resolution	Black (text and graphics): Up to 300 x 300 dpi; Up to 300 x 300 dpi Color (text and graphics): Up to 300 x 300 dpi
Maximum number of copies	Up to 9 copies
Copier settings	Auto-enlarge
Fax resolution	Black (best): Up to 150 x 150 dpi; Color (best): 150 x 150 dpi; Black (standard): 150 x 150 dpi; Color (standard): 150 x 150 dpi
Fax speed	14.4 kbps
Fax smart software features	Option to add files from your phone file/photos, Camera scan or Printer scanner, Option to easily add cover page and save the cover page template, Access to Fax history to see all send faxes and drafts, Ability to edit and resent fax from History, Easily print fax confirmation
Fax Features ⁹	Fax memory: Unlimited storage; Auto fax reduction supported: No; Auto-redialing: Yes; Fax delayed sending: No; Distinctive ring detection supported: No; Fax forwarding supported: Yes; Fax phone TAM interface supported: No; Fax polling supported: No; Fax telephone mode supported: No; PC interface supported: Yes, using HP Smart app for Desktop; Remote retrieval capability supported: Yes (with HP Smart app using mobile device)
Standard connectivity	1 Hi-Speed USB 2.0
Network capabilities	Yes, built-in Wi-Fi 802.11 a/b/g/n
Wireless capability	Yes, built-in Wi-Fi 802.11 a/b/g/n
Mobile printing capability ⁶	HP Smart app; Apple AirPrint™; Mopria™-certified
Memory	Standard: 86 MB; Maximum: 512 MB DDR1; 160 MB flash
Processor speed	180 MHz/Hard disk: No
Duty cycle	Monthly, letter: Up to 1000 pages
Recommended monthly page volume	100 to 300
Media types supported	Plain paper, photo paper, brochure paper, envelopes and other specialty inkjet papers
Media weight supported	Letter: 16 to 32 lb; HP envelopes: 20 to 24 lb; HP cards: up to 110 lb; HP 4 x 6 inch photo paper: up to 145 lb
Media sizes supported	Letter; legal; 4 x 6 in; 5 x 7 in; 8 x 10 in; No. 10 envelopes
Media Sizes Custom	3 x 5 to 8.5 x 14 in
Paper handling	Input Capacities: Up to 60 sheets Standard; Up to 5 envelopes; Up to 20 cards; Up to 10 sheets Labels; Up to 60 sheets Legal Auto Document Feeder: Standard, 35 sheets Output Capacities: Up to 25 sheets Standard; Up to 5 envelopes; Up to 20 cards; Up to 10 sheets Labels; Up to 25 sheets Legal Duplex Options: Manual (driver support provided) Envelope feeder: No Standard paper trays: 1

What's in the box ⁸	3XV13A HP DeskJet 4155 All-in-One; HP 67 Setup Black Instant Ink Ready Cartridge; HP 67 Setup Tri-color Instant Ink Ready Cartridge; Regulatory flyer; Setup guide; Reference guide; Power cord (1.5 m) [For ink volume and page yield information, visit http://hp.com/go/learnaboutsupplies]
Replacement cartridges ⁴	HP 67 Black Original Ink Cartridge (~120 pages yield) 3YM56AN; HP 67XL Black High Yield Original Ink Cartridge (~240 pages yield) 3YM57AN; HP 67XXL Black Extra High-Yield Original Ink Cartridge (~400 pages yield) 3YM59AN; HP 67 Tri-Color Original Ink Cartridge (~100 pages yield) 3YM55AN; HP 67XL Tri-Color High-Yield Original Ink Cartridge (~200 pages yield) 3YM58AN; HP 67XXL Tri-Color Extra High-Yield Original Ink Cartridge (~330 pages yield) 6ZA16AN.
Instant ink eligible	HP Instant Ink eligible / Save up to 50% on ink. For more information visit http://www.hpinstantink.com
Product dimensions	W x d x h: 16.85 x 13.07 x 7.87 in; Maximum: 16.8 x 22.8 x 10.3 in (Output Extension Fully Out)
Product weight ⁷	10.6 lb
Warranty features	One-year limited hardware warranty; 24-hour, 7 days a week support
Control panel	Fixed icons display; 7 buttons (Power, Cancel Job, Resume, Info, Wireless, Color Copy & Black Copy); 5 LED indicator lights (Power, Ink level, Wifi, resume & Info).
Display description	Icon LCD display
Software included	WW: HP Printer Software, available online; AP Indo: CD Software included
Compatible operating systems	Windows 10, 7; MacOS Sierra v10.12 (previously OS X), macOS High Sierra v10.13, macOS Mojave v10.14, macOS Catalina v10.15
Compatible network operating systems	Windows 10, 7; MacOS Sierra v10.12 (previously OS X), macOS High Sierra v10.13, macOS Mojave v10.14, macOS Catalina v10.15
Minimum system requirements	PC: Windows 10, 7: 1 GHz 32-bit (x86) or 64-bit (x64) processor, 2 GB available hard disk space, Internet connection, USB port, Internet Explorer.; Mac: MacOS Sierra v10.12 (previously OS X), macOS High Sierra v10.13, macOS Mojave v10.14, macOS Catalina v10.15, 2 GB Available Space, Internet Access.
Power ²	Power supply type: internal; Power requirements: Input voltage: 100 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3 Hz). Input voltage: 200 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3Hz) (China & India) Power consumption: 1.0 watts (sleep), 0.1 watts (off), 0.1 watts (auto-off)
Acoustics	Acoustic power emissions: 6.4 B(A)
Operating environment	Operating temperature range: 41 to 104°F; Recommended operating temperature: 59 to 86°F; Storage temperature range: -40 to 140°F; Non-operating humidity range: 5 to 90% RH (non-condensing); Operating humidity range: 15 to 80% RH (non-condensing); Recommended humidity operating range: 20 to 80% RH (non-condensing)
Accessories	None

Learn more at
<http://www.hp.com>

¹ Dimensions vary as per configuration ² Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. ³ Speed specifications have been updated to reflect current industry testing methods. ⁴ Average based on ISO/IEC 24711 or HP testing methodology and continuous printing. Actual yield varies considerably based on content of printed pages and other factors. For details see <http://hp.com/go/learnaboutsupplies> ⁵ Either after first page or after first set of ISO test pages. For details see <http://www.hp.com/go/printerclaims> ⁶ Wireless performance is dependent upon physical environment and distance from the access point. Wireless operations are compatible with 2.4 GHz routers only; excludes wireless direct. Wireless direct may require driver or apps be installed and connected on wireless-enabled mobile device or PC. Wireless functionality may vary by computer and mobile operating systems, see <http://hpconnected.com>. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary. AirPrint supports OS X v10.11 El Capitan and devices running iOS 4.2 or later and requires the printer be connected to the same network as your OS X or iOS device. AirPrint, the AirPrint Logo, iPad, iPhone, and iPod touch are trademarks of Apple® Inc. Windows is a trademark of the Microsoft group of companies. ⁷ Weight vary as per configuration ⁸ For more information about page yields for replacement cartridges see <http://hp.com/go/learnaboutsupplies> for setup cartridges click on Setup supplies link on the same page. ⁹ Based on cloud storage ¹⁰ Set by Fax service Provider

