



TP6

All-in-One POS Terminal

With a sleek yet robust design, the TP6 is the perfect enterprise-grade POS solution. The TP6 features a 15" TruFlat projected capacitive touchscreen, a range of Intel CPUs, cable free accessories and a versatile dual hinge design.



CHARACTERISTICS

RESILIENT TOUCH DISPLAY

The TP6 features a 15" LCD screen with TruFlat projected capacitive (PCAP) multi-touch technology built to take the rigors of heavy use.

VERSATILE PLATFORM

A dual hinge design allows for efficient shipping and almost unlimited tilt angles. Built-in VESA mounting extends the versatility of the platform to any wall mount installation.

FAN-LESS DESIGN

A fan-less design provides a sleek, clean look and silent operation. No vent openings mean better protection from dust and water reaching an IP54 ingress protection rating.

EFFICIENT HIGH PERFORMANCE CPUs

With support for Intel CPUs ranging from the efficient J1900 to the powerful Core i5, the TP6 is sure to fit any application

ACCESSORIES

- Card Reader (MSR)
- Biometric Reader
- 2-line Rear Display
- 10.1" Rear Display
- Attached Augusta Reader Bracket

What is in the box:

AIO POS Terminal, AC Power Adapter + Cord, RJ45 to DB9 Serial Cable

TECHNICAL SHEET

MODEL	TP6D-F	TP6D-3	TP6D-5	TP6W-3
Processor	Intel Celeron J1900	Intel Core i3-6100U	Intel Core i5-6200U	Intel Core i3-6100U
Bezel	TruFlat Bezel			
Chip Set	Processor Integrated			
System Memory	1 x DDR3L SO-DIMM 4GB - 8GB		1 x DDR3L SO-DIMM 8GB	
Hard Drive	2.5" 64-500GB SSD or 2.5" 500GB HDD			
LCD Display	15" (381mm) TFT LCD		18.5" (470mm) TFT LCD	
Resolution	1024x768		1920x1080	
Touch	PCAP,10 Point Multi-Touch			
Brightness	300 nits		350 nits	
Graphic Engine	Intel HD Graphics DX11 and OCL1.1		Intel HD Graphics DX12 and OCL4.2	
TPM	N/A		2.0	
Electrical	65W/19V		90W/19V	
Supported OS	Win 7 Pro (x32/x64), POSReady 7(x32/x64), Win 10 IoT(x32/x64)		Win 8.1 Embedded (x64),Win 8.1 Pro (x64),Win 10 IoT (x64),Win 10 Pro (x64)	

PORTS

I/O	4 x USB 2.0 / 1 x USB 3.0 3 x RJ45 with 0V/5V/12V power Serial 1 x RJ45 LAN Dual Band 802.11 a/b/g/n/ac 2.4GHz/5GHz 1 x RJ11 (12V/24V) Cash Drawer Port 1 x DB15 VGA	2 x USB 2.0 Type A / 4 x USB 3.0 3 x RJ45 with 0V/5V/12V power Serial 1 x RJ45 LAN Dual Band 802.11 a/b/g/n/ac 2.4GHz/5GHz 1 x RJ11 (12V/24V) Cash Drawer Port 1 x DB15 VGA	2 x USB 2.0 Type A / 4 x USB 3.0 3 x RJ45 with 0V/5V/12V power Serial 1 x RJ45 LAN 1 x RJ11 (12V/24V) Cash Drawer Port 1 x DB15 VGA
-----	---	--	---

PHYSICAL

Housing	Die Cast Aluminum			
Weight	13.2 lbs		9.6 lbs	
Dimensions (w/base) (WxDxH)	14.2" x 8" x 10.9"		18.1" x 8" x 11.4"	
Tilt	Dual Hinge			
Housing Color	Black			
Wall Mount	100mm VESA (75mm or 100mm with base)			

ENVIRONMENTAL

IP Rating	IP54 (Front) Splash Resistant Screen			
Operating Temperature	32°F - 95°F (0°C - 35°C)			
Humidity	20%- 80%RH non-condensing			
Certifications	FCCClass B, CE, LVD, NOM			
Viewing Angle	Horizontal: 140°, Vertical 130°			
Warranty	3 years			

MODELS



935KY402Y00L33

15", Celeron J1900, 4GB, 120GB
SSD, Win 10 IoT x64



935KY400200L33

15", Core i3 6100U, 4GB, 120GB
SSD, No O/S



935KY401700L33

15", Core i3 6100U, 8GB, 500GB
SSD, Win 10 IoT x64



935KY402300L33

15", Core i5 6200U, 8GB, 500GB
SSD, Win 10 Pro x64

Via Berettine, 2 - 43010 Fontevivo PR - VAT: IT02498250345 - TEL: +39 0521 680111 - FAX: +39 0521 610701 - UNIQUE CODE: 8RQN7AZ

The technical data on this website are not binding and may be changed without advanced notice.

Last update: 11 July 2024