

The USB-C 3-in-1 Mini Dock with HDMI, USB-A and USB-C Power Delivery connects to USB-C or Thunderbolt™ 3 enabled laptops and is perfect for contributing to a desktop solution making it ideal for inside reps that need essential connectivity while in the office or when working from home.

This USB-C mini dock supports up to 100W of power delivery to charge and power mobile laptops when using the USB-C power adapter that is included with the laptop. The maximum power capacity depends on how much power the connected adapter can supply. The right amount of power is necessary to keep the laptop battery charged, for all connected devices to function, and for the dock to provide that connectivity.

This mini dock includes an HDMI port with a resolution up to 4K (3840 x 2160) at 60Hz for high definition audio/video. The USB-A and USB-C data ports support SuperSpeed USB 5Gbps data transfer allowing up to 32GB of data to be downloaded in under a minute. Optimize performance by connecting displays designed for 4K 30Hz signals and USB devices designed for 5Gbps transfer speeds.

PORTS

4K HDMI: Connect to a 4K display via the HDMI port.

USB-A: Connect storage devices and transfer data up to 5Gbps through the USB-A port.

USB-C Data and PD: Transfer data up to 5Gbps from a storage device and power a laptop or tablet with up to 100W power delivery.

Additional Technical Specifications

Signal Specifications

- HDMI Resolution: Up to 4K (3840x2160) @ 60Hz
- USB-A 3.0 Female: Supports Data up to 5Gbps
- USB-C Female: Supports PD 3.0 Charging



Electrical Specifications

- Cable: OD: 4.2MM, Jacket PVC

Physical Specifications

- Operating Temperature: 0° to 50°C
- Storage Temperature: -25° to 70°C

Physical Characteristics

- Connector: HDMI A Female: Contact Pin: C5191, Gold Plated Shell: C2680, Nickel Plated Insulation: LCP, Black
- Connector: USB-C Female: Contact Pin: Copper Alloy, Gold Plated Shell: Stainless Steel, Nickel Plating Insulation: LCP, Black
- Connector: USB-A 3.0 Female: Contact Pin: Copper Alloy Shell: SUS, Nickel Plating Insulation: LCP, Blue
- Connector: USB-C Male: Contact Pin: Copper Alloy, Gold Plated Shell: Stainless Steel, Nickel Plating Insulation: LCP, Black
- AL Shell: Gray
- AL Shell: Gray/Printing: C2G
- Shell: Back Cover: ABS+PC/Black
- Inspection: 100% Test for Short/Open
- Inspection: Mechanical test for Connectors
- Inspection: 100% Function Test

Features & Benefits

Supports up to 100W of power delivery to keep your laptop charged Supports HDMI resolutions up to 4K, for viewing your screen content at full HD

USB-A and USB-C ports for fast data transferring

Reversible, symmetrical USB-C connector, so no guessing how to plug it into your laptop

Plug-and-play, no additional software or drivers needed

5 year warranty, for peace of mind – with the highest quality docking stations

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120544609	Country Of Origin	China
Features	Compact, USB-A Charging, USB-C Charging	Works With	Windows, MacOS, Linux
Application Sector	Residential, Commercial	Warranty Type	5-Year
Type	Docking Station, Active Device		

Dimensions

Product Width US	2.95 in	Product Depth US	1.5 in
Product Height US	0.59 in		

Listing Agencies / 3rd Party Agencies

CE Certified	Yes
--------------	-----

Technical Information

Video Resolution	4K 60Hz, 4K 30Hz, 4K, 1080p	USB Power Output	100 W
Amperage	5 A	Data Transfer Rate	10 Gbps
Adapter Rear	HDMI Female, USB 3.0 A Female, USB-C Female	Adapter Front	USB-C Male