

## PERFORMANCE

### Panel

#### Panel

In-Plane Switching (IPS)

#### Display Size

21.5 inches (546.1mm)

#### Max View Area

WxH: 476.1 x 267.8 mm (18.74 x 10.54 inches)

#### Native Resolution

1920x1080

#### Aspect Ratio

16:9

#### Pixel Pitch

0.24795 x 0.24795 mm

#### DPI

102.4 dpi

#### Brightness

250 nits

#### Contrast Ratio

1000:1

#### Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

#### Color Gamut

72% NTSC

#### Anti Reflective

Anti-glare

#### Viewing Angle

horizontal: +/- 89°, vertical: +/- 89°

### Multi-Media

#### Camera

720p, with dual microphone and Think Shutter

#### Microphone

Dual array microphone

#### Speakers

Stereo speakers, 2W x2

### Power Supply

#### Power Supply

Power	Type	Efficiency	Key Features
90W	Adapter	88%	-

#### Power Consumption

14 watts typical, 25 watts max

## DESIGN

### Menu

#### Presets and User Setting

- Presets: 25

# ThinkCentre Tiny-In-One 22 Gen 4

- User settings: 25

## On Screen Display

On screen display with digital user controls (8 languages)

## Display

### Touchscreen

(Optional)Advanced In-cell Touch (AIT), supports 10-point touch. ONLY for model 11GTPAT1 and 11GTPAR1.

## Mechanical

### Compatible Tiny

P340 / P330 / P320 / M90q / M80q / M70q / M75q / M920(x) / M720 / M910(x) / M710 / M715 / M900(x) / M700 / M630e / M625 / M600 Tiny/ M90n / M75n Nano (with TIO kit)

### Bezel Width

- Top / Side: 2mm
- Bottom: 22.1mm

### Buttons

- Power button
- Exit button
- Menu button
- Mode-switching button
- Brightness button

### Cables

Undetachable 3-in-1 cable (Power connector, USB [supports USB 3.1 Gen1 / USB 2.0], DisplayPort™)

### Case Color

Black

### Dimensions (WxDxH)

Models	Dimensions
Models without stand	489 x 65.3 x 339 mm (19.26 x 2.57 x 13.35 inches)
Models with full function monitor stand	489 x 220.4 x 568.2 mm (19.26 x 8.68 x 22.37 inches)

### Weight

Models	Weight
Models without stand	3.41 kg (7.52 lbs)
Models with full function monitor stand	6.58 kg (14.51 lbs)

### Mounting

Supports VESA mount (100mm)

### Stand

Full function monitor stand, supports -5° to +30° tilt, left & right 45° swivel, up to 150mm lift, -5° to +90° Pivot

### In the Box

- TIO (Monitor)
- Detachable Stand
- Driver CD
- Information Flyer
- Power Adapter
- Power Cord
- User's Guide

## CONNECTIVITY

### Ports

#### Rear Ports

- 1x USB upstream port
- 1x DisplayPort
- 1x power connector

## Left Ports<sup>[1]</sup>

- 1x USB Type A (on TIO)
- Side ports offered by installed Tiny (on Tiny)

### Notes:

1. The availability and version depends on the Tiny installed or the PC connected via USB upstream port

## SERVICE

### Warranty

#### Base Warranty

3-year customer carry-in or mail-in via rapid replacement service

## CERTIFICATIONS

### Green Certifications

#### Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 5
- GREENGUARD®
- TCO Certified 8.0
- TCO edge 2.0
- RoHS compliant
- WEEE

### Other Certifications

#### Other Certifications

TÜV Eye comfort certified

