



C2G
20ft (6.1m) C2G Performance Series Premium High Speed HDMI® Cable - 4K 60Hz In-Wall, CMG (FT4) Rated
Part No. CG-50188



This Premium High Speed HDMI Cable supports all HDMI 2.0 features and have been tested to conform with the Premium HDMI Cable Certification Program for highest performance and ultra-reliability. This cable is ideal for HD Blu-ray and HD DVD video, experiencing resolutions up to 4K (4096 x 2160 at 60hz, 4:4:4), bandwidths up to 18Gbps, HDR for higher contrast ratios and vivid colors, plus 32 uncompressed digital audio channels to provide crystal-clear sound, making it perfect for home theater applications or digital signage.

Convenience

This cable is designed to exceed the highest measure of HDMI performance and will enhance video experiences with higher resolutions, increased speeds, sharper images and are backward compatible with previous HDMI specifications for existing HDMI devices. They also deliver dual video streams, so that two videos can be viewed simultaneously on a single display.

Performance

Each length of these cables have been tested to deliver the full 18Gbps bandwidth required by the specifications for Premium High Speed HDMI certification.

Note: Your display must support Multi-View in order to take advantage of dual video streams.

Features & Benefits

- Supports all HDMI 2.0 features including resolutions up to 4K (4096 x 2160 at 60hz, 4:4:4)
- Supports 3D and dual video streams (Dual View)
- Data speeds up to 18.0Gbps
- Supports full HD Blu-ray and HD DVD video
- Supports 8, 10, 12, and 16bit per channel Deep Color
- Supports up to 32 audio channels and a 1536kHz audio sampling rate
- Supports DTS-HD Master Audio™, Dolby TrueHD™, DTS, Dolby AC3 and DSD Audio
- Supports extended CEC (Consumer Electronics Control) commands and functions, HDMI Ethernet Channel (100Mbps/s), and ARC (Audio Return Channel)

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120501886	Country Of Origin	China
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	20 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Video Resolution	4K 60Hz, 4K 30Hz, 4K, 1080p	Bend Radius	90 mm
Cable Type	High Speed HDMI, Video, Premium HDMI	Jacket Rating	CMG (FT4) Rated

Data Transfer Rate	18 Gbps	Adapter Rear	HDMI Male
--------------------	---------	--------------	-----------

Adapter Front	HDMI Male
---------------	-----------
