



This USB Active Extension Cable is an ideal solution for USB applications which require more cable length than the 5 meter (16.5ft) length limitation of USB. This extension cable actively buffers the incoming and outgoing signals to ensure compliance with the USB 2.0 specification for electrical and timing minimums. The plenum rated jacket meets the requirements for an installation in a commercial space, and both low and high speed USB devices will function equally well with this extension.

Features & Benefits

- Plenum, CMP-rated jacket
- Supports USB 2.0 bandwidth
- Draws power required for operation through the USB port

Specifications

General Info

Product Line	C2G	UPC Number	757120399353
Country Of Origin	China	Application Sector	Residential, Commercial
Warranty Type	3-Year	Type	Cable

Dimensions

Cable Length	50 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Wire Gauge	24 AWG	Bend Radius	60 mm
------------	--------	-------------	-------

Cable Type	USB, Active Copper Cable, Extension	Jacket Rating	CMG (FT4) Rated
Data Transfer Rate	480 Mbps	Adapter Rear	USB-A Female
Adapter Front	USB-A Male		
