




Phone: 802-874-0123
Fax: 703-991-8770
Email: sales@tsitouch.com
tsitouch.com

Samsung 75" UHD Projected Capacitive Touch Screen Solution



Samsung Authorized Solution

SAMSUNG



Projected Capacitive Touch Solution

TSitouch's line of projected capacitive touch displays are engineered specifically for consumer and commercial customers who are looking for a rugged and durable touch screen without having to sacrifice on image quality. Featuring a seamless flat front bezel design, the monitor can easily be wiped clean, thereby eliminating having to worry about dust and dirt collection, which helps extend the use of your display and enhances your touch experience.



Multi-Touch Screen
True multi-touch support with up to 100 simultaneous touch points for all major operating systems



Easy Integration
Unrivaled simplicity makes installation easier and faster



Ultra-Fast Response Time
Allows for split second reactions between touch point and screen



HID Compliant
Maximum compatibility with numerous operating systems, plug-and-play



Superior Design
Zero bezel flat front, clear tempered touch screen with excellent optical performance



Easy to Clean
Water and dust resistant

Specifications

Display Models	QB75R, QH75R, QM75R
Touch Screen (Display Not Included)	TSI75NS15DHJCZZ
QB75R Integrated Touch Screen (Display Included)	TSI75PSSBDHJCZZ
QH75R Integrated Touch Screen (Display Included)	TSI75PSQCDHJCZZ
QM75R Integrated Touch Screen (Display Included)	TSI75PSDCDHJCZZ
Protective Glass	3/16" Clear Tempered Cover Glass
Structure Material	Black Powder Coated Cold Rolled Steel
Touch Technology	PCAP
Touch Points	40
Response Time	6 - 16ms
Touch Accuracy	+/- 2mm (Over 99% Area)
Interface	Type A USB/M
Communication	USB 2.0
Receiver Extender	N/A
Touch Power Source	USB
Width/Height/Depth Including Monitor	50.35" x 29.49" x 2.32"
Touch Screen Weight	81.57 lbs
Display Integrated Weight	166.01 lbs
Boxed Dimensions	70.00" x 42.50" x 7.50"
OS Support	Windows, Google Chrome, Android, Mac, Linux

Specifications and designs are subject to change without notice
Non-metric weights and measurements are approximate