



19" Double Section Wallmount Cabinet, 15U, 600 mm (23.6 in.) Depth, Black

Flat Pack, Steel Panels, Maximum Static Load 30 kg, Reversible Front Door

Part No.: **713887**

EAN-13: 0766623713887 | UPC: 766623713887

Intellinet Network Solutions Double-Section wallmount cabinets offer you a flexible solution for your network installations. Since they ship flat-pack (unassembled)*, they save you space and money. High quality features include a 4MM toughened glass door and cold-rolled galvanized steel. The rear door access to the back of the cabinet makes cabinet and component exchange a breeze.

*Completely assembled versions are available in certain countries.

Features:

- Flat Pack Design
- Ideal for 19" rackmount applications
- Maximum static load of 30 kg
- Usable depth: 279 mm (10.98 in.) to 359 mm (14.13 in.)
- Cable entry via rear or top panel
- 4MM toughened glass door

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Rear door for easy access to back of cabinet
- Reversible Front door
- Cold-rolled, galvanized SPCC steel with up to 1.5 mm thickness
- Ships Flatpacked
- Three-Year Warranty

Specifications:

General

- 19"
- Height: 15U
- Color: Black RAL7021
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Physical

- 725 (h) x 540 (w) x 600 (d) mm
- 28.54 (h) x 21.26 (w) x 23.62 (d) in.
- Usable depth: 279 mm (10.98 in.) to 359 mm (14.13 in.)
- Maximum static load: 30 kg (66 lbs.)

Package Contents

- 2 Rail frames
- Top, Bottom, Front, Back & Side Panels
- Installation hardware including 20x M6 Sets and 4x Keys



