



High Speed HDMI Cable

ARC, 3D, 4K@30Hz, HDMI Male to Male, Shielded, 1 m (3 ft.), Black

Part No.: **308816**

EAN-13: 0766623308816 | UPC: 766623308816

A high-speed cable to deliver high-definition performance

HDMI has become the standard digital connection, delivering the highest-quality audio and video signal over a single cable. The Manhattan High Speed HDMI Cable is designed and carefully constructed to meet the evolving needs of the high-definition marketplace. This shielded cable provides the highest resolution possible at 4K x 2K, an audio return channel and a bandwidth of 10.2 Gigabits per second at 600 MHz. A high-quality HDMI cable, it provides high-definition video and multi-channel, digital audio with increased performance characteristics, greater accuracy and expanded features.

Features:

- 4K@30Hz Ultra-High-Definition (UHD) resolution supports video resolution beyond 1080p; up to 1080p resolution in 3D and Deep Color
- Compatible with any HDMI device, such as Blu-ray, game consoles, stereos, PCs and more
- Audio Return Channel (ARC) transmits TV audio through your sound system; no need for additional cable
- Fully shielded to reduce EMI and other interference sources
- Tangle-resistant design allows for easier handling and management; resists cuts and nicks
- Ensures the integrity of the signal between HDMI devices
- Compliant with High Speed HDMI specifications
- Up to 10.2 Gbps at 340 MHz bandwidth
- Lifetime Warranty

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

Specifications:

Standards and certifications

- ISO9001

General

- Bandwidth: 10.2 Gbps at 340 MHz
- Meets or exceeds existing HDMI standards
- Length: 1 m (3 ft.)

Connectors

- Two HDMI 19-pin male
- Gold-plated contacts
- Molded PVC boot
- Built-in strain relief

Cable

- 30 AWG cable
- Double shielded
- Current rating: 0.5 A DC
- Withstanding voltage: 300 V DC
- Insulation resistance: 5 MOhms
- Conductive resistance: 1 Ohms
- Thermal plastic casing

Operating Environment

- Operation Temperature: 32 – 104°F (0 – 40°C)
- Storage Temperature: -4 – 140°F (-20 – 60°C)
- Humidity (noncondensing): 0 – 96%

Package Contents:

- High Speed HDMI Cable



