

High Speed HDMI Cable

ARC, 3D, 4K@30Hz, HDMI Male to Male, Shielded, 1.5 m (5 ft.), Black

Part No.: 355308

EAN-13: 0766623355308 | UPC: 766623355308

A high-speed cable that delivers high-definition performance.

HDMI has become the standard digital connection, delivering the highest-quality audio and video signal over a single cable. The Manhattan High Speed HDMI Cable is designed and carefully constructed to meet the evolving needs of the high-definition marketplace. This shielded cable provides the highest resolution possible at 4K x 2K, an audio return channel and a bandwidth of 10.2 Gigabits per second at 340 MHz. Offering a high-quality connection between HDMI-enabled sources and displays, the Manhattan High Speed HDMI Cable provides ultra-high-definition video and multichannel, digital audio with increased performance characteristics and greater accuracy.

Features:

- 4K@30Hz Ultra-High-Definition (UHD) resolution supports video resolution up to four times that of 1080p; supports up to 1080p resolution in 3D and Deep Color
- Audio Return Channel (ARC) transmits TV audio through your sound system; no need for additional cable
- Tangle-resistant design allows for easier handling and management; resists cuts and nicks

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Ensures the integrity of the signal between HDMI devices
- Compliant with High Speed HDMI specifications
- Provides bandwidth up to 10.2 Gbps at 340 MHz
- Fully shielded to reduce EMI and other interference sources
- Compatible with any HDMI device, such as Blu-ray, game consoles, stereos, PCs and more
- Lifetime warranty

Specifications:

Standards and certifications
• ISO9001

General
• Bandwidth: 10.2 Gbps at 340 MHz
• Meets or exceeds existing HDMI standards
• Length: 1.5 m (5 ft.)

Connectors
• Two HDMI 19-pin male
• Gold-plated contacts
• Molded PVC boot
• Built-in strain relief

Cable
• 30 AWG cable
• Double shielded
• Current rating: 0.5 A DC
• Withstanding voltage: 300 V DC
• Insulation resistance: 5 MOhms
• Conductive resistance: 5 Ohms
• Thermal plastic casing

Operating Environment
• Operation Temperature: 0 – 40°C (32 – 104°F)
• Storage Temperature: -20 – 60°C (-4 – 140°F)
• Humidity (noncondensing): 0 – 96%

Package Contents
• High Speed HDMI Cable

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.











For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.