



16-Port Gigabit Ethernet PoE+ Switch with 4 RJ45 Gigabit and 2 SFP Uplink Ports

IEEE 802.3at/af Power over Ethernet (PoE+/PoE) Compliant, 300 W, Endspan, 19" Rackmount

Part No.: **561419**

EAN-13: 0766623561419 | UPC: 766623561419

The Intellinet Network Solutions 16-Port Gigabit Ethernet PoE+ Switch with 4 RJ45 Gigabit and 2 SFP Uplink Ports passes both data and electrical power to a number of PoE-compatible devices via standard network cables. Equipped with 16 Gigabit Ethernet ports, the switch can power wireless LAN access points and bridges, VoIP phones, IP video cameras and more while delivering network speeds of up to 1,000 Mbps.

Power over Ethernet 802.3at

This high-powered switch supports the IEEE 802.3at Power over Ethernet protocol and can inject up to 32 watts of power per port*. IEEE802.3af- or IEEE802.3at-compliant devices attached to the switch require no additional power, which eliminates the time and expense of electrical rewiring and minimizes the unsightly clutter caused by power supplies and adapters in awkward places such as ceilings and walls. Any mix of PoE and non-PoE devices is supported. Thanks to its built-in short-circuit-, overload- and high-voltage-protection functions, your equipment is well-protected. For devices that are not 802.3at/af compliant (e.g., legacy wireless access points or network cameras), we suggest the use of an Intellinet Network Solutions PoE/PoE+ Splitter.

Equipped with 16 auto-sensing 10/100/1000 Mbps RJ45 Gigabit Ethernet ports, four RJ45 and two SFP uplink ports, the Intellinet Network Solutions switch offers plenty of performance for your computers, servers and other networking devices.

Total PoE budget for this switch is 300 watts. Per-port average power distribution is 18.75 watts; maximum per-port power usage cannot exceed 32 watts.

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

Features:

- Provides power and data connection for up to 16 PoE network devices
- Saves time and money by delivering data and power via existing network cables
- 10/100/1000 auto-sensing ports automatically detect optimal network speeds
- IEEE 802.3at/af-compliant RJ45 PoE/PoE+ output ports
- Power output up to 32 watts per port*
- Manual PoE extend mode (reduces network speed and extends PoE support to 250 m)
- Manual VLAN mode (allows ports 1 through 16 to be isolated from each other)
- PoE power budget of 300 watts
- Four RJ45 Gigabit and two SFP uplink ports
- Supports IEEE 802.3at and IEEE 802.3af-compliant PoE devices (e.g., wireless access points, VoIP phones, IP cameras)
- Supports IEEE 802.3at/af detection and short circuit, overload and high-voltage protection
- Complies with the IEEE 802.3az (Energy Efficient Ethernet EEE) specification
- Green Ethernet power-saving technology deactivates unused ports and adjusts power levels based on the cable length
- All RJ45 ports with Auto-MDIX (auto uplink) support
- Store and forward switching architecture
- IEEE 802.3x flow control for full duplex
- Supports up to 8192 MAC address entries, Auto-Learning and Auto-Aging
- Cooling fan for ventilation
- Fully NDAA-compliant
- Three-year warranty

Specifications:

Standards

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3ab (Twisted Pair Gigabit Ethernet)
- IEEE 802.3af (Power over Ethernet 802.3af Type 1)
- IEEE 802.3at (Power over Ethernet 802.3at Type 2)
- IEEE 802.3az (Energy Efficient Ethernet EEE)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3x (flow control for full duplex mode)

General

- Media support:

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- 10Base-T
- 100Base-TX
- 1000Base-T
- Packet filter/forwarding rate:
 - 1,488,000 pps (1000 Mbps)
 - 148,800 pps (100 Mbps)
 - 14,880 pps (10 Mbps)
- MAC address table: 8192 entries
- Buffer memory: 4.1 MB
- Backplane speed: 44 Gbps
- Switch architecture: store and forward
- MTBF: > 50,000 hours
- Cooling
 - Two cooling fans
- Pinout RJ45 output ports (Data + Power)
 - IEEE Alternative A
 - Pin 1: Vport [+]
 - Pin 2: Vport [+]
 - Pin 3: Vport [-]
 - Pin 4: Unused
 - Pin 5: Unused
 - Pin 6: Vport [-]
 - Pin 7: Unused
 - Pin 8: Unused
- Certifications: FCC Class A, CE, RoHS

LEDs

- Power
- PoE
- Link/activity/speed

Power

- Input: 100 – 240 V AC, 50 – 60 Hz
- Power consumption: 300 watts (maximum)

Physical

- Metal housing
- Dimensions: 230 (L) x 440 (W) x 44 (H) [mm] / 9.06 (L) x 17.32 (W) x 1.73 (H) [in]
- Weight: 5 kg (11.2 lbs.)

Environmental

- Operating temperature: 0 – 40°C (32 – 104°F)
- Storage temperature: -40 – 70°C (-40 – 158°F)
- Operating humidity: 10 – 90% RH, non-condensing
- Storage humidity: 5 - 90% non-condensing

Package Contents

- 16-Port Gigabit Ethernet PoE+ Switch with 4 RJ45 Gigabit and 2 SFP Uplink Ports
- Power cable
- User Guide
- Rubber feet
- 19" mounting brackets

