

Entry-level IP Phone with 2 Lines & HD voice

As a very fashionable and friendly entry-level IP phone, Yealink SIP-T31P has an extra-large 132x64-pixel graphical LCD with backlight that brings clear visual experience for users. The T31P offers support for two VoIP accounts and includes local 5-way conferencing to maximize productivity. Working with the adjustable multi-angle stand, the T31P IP phone ensures you to work in different situation. Meanwhile, the T31P features built-in Power over Ethernet (PoE) and superb high definition (HD) sound quality. Easy-to-use and powerful features together with reasonable price deliver excellent voice communications solution.



Unified
Firmware



Elegant
Industrial Design



EHS



Device
Management



HD



Opus



5-way
Conferencing



Key Features and Benefits

Stronger Performance, More Possibilities

Equipped with powerful chip, the T3 series owns a stronger computing ability and more upgraded functions, which ensures a higher productivity and smoother office experience. Due to great performance, T3 series is capable to extend more services for different business demands.

Superior HD Audio, Better Communication

The Yealink T3 series provides distraction-free communications with industry leading Smart Noise Filtering Technology, which delivers excellent sound quality without extraneous noises and allows fluent conversations.

Classic Design, Practical Details

Designed by Yealink original team, T3 series inherits the design concept of Yealink IP phone family. The advanced design including modern appearances and ergonomic details enables easier and friendly operation experience to users.

All in One Platform, Convenient Management

Proven reliability and integrations for Yealink Device Management Platform, installed the unified firmware, T3 series is simple to deploy and manage, which allows a significant reduction in the operation and maintenance cost.

- Yealink HD Voice
- 2.3" 132x64-pixel graphical LCD with backlight
- Two-port 10/100M Ethernet Switch
- PoE support
- Opus codec support
- Up to 2 SIP accounts
- Local 5-way conferencing
- Support EHS Wireless Headset
- Unified Firmware
- Support YDMP/YMCS
- Stand with 2 adjustable angles
- Wall mountable

Audio Features

- HD voice: HD handset, HD speaker
- Smart Noise Filtering
- Wideband codec: Opus, G.722
- Narrowband codec: G.711(A/μ), G.723.1, G.729, G.729A, G.726, iLBC
- DTMF: In-band, Out-of-band (RFC 2833) and SIP INFO
- Full-duplex hands-free speakerphone with AEC
- VAD, CNG, AEC, PLC, AJB, AGC

Phone Features

- 2 VoIP accounts
- Call hold, mute, DND
- One-touch speed dial, hotline
- Call forward, call waiting, call transfer
- Group listening, SMS, emergency call
- Redial, call return, auto answer
- Local 5-way conferencing
- Direct IP call without SIP proxy
- Ring tone selection/import/delete
- Set date time manually or automatically
- Dial plan
- XML Browser, action URL/URI
- Integrated screenshots
- RTCP-XR, VQ-RTCPXR
- Enhanced DSS Key

Directory

- Local phonebook up to 1000 entries
- Black list
- XML/LDAP remote phonebook
- Smart dialing
- Phonebook search/import/export
- Call history: dialed/received/missed/forwarded

IP-PBX Features

- Busy Lamp Field (BLF), Bridged Line Appearance (BLA)
- Anonymous call, anonymous call rejection
- Hot-desking, voice mail
- Flexible seating
- Call park, call pickup
- Executive and Assistant
- Centralized call recording
- Visual voice mail
- Call recording

Display and Indicator

- 2.3" 132x64-pixel graphical LCD with backlight
- LED for call and message waiting indication
- Dual-color (red or green) illuminated LEDs for line status information
- Intuitive user interface with icons and soft keys
- Multilingual user interface
- Caller ID with name and number
- Power saving

Feature keys

- 2 line keys with LED
- 6 features keys: transfer, message, headset, redial, mute, hands-free speakerphone
- 5 navigation keys
- Volume control keys

Interface

- 2 x RJ45 10/100M Ethernet ports
- Power over Ethernet (IEEE 802.3af), class 2
- 1 x RJ9 (4P4C) handset port
- 1 x RJ9 (4P4C) headset port

Other Physical Features

- Color: Classic Grey
- Wall mountable
- External Yealink AC adapter
AC 100~240V input and DC 5V/600mA output
- Power consumption (PSU): 2-3W
- Power consumption (PoE): 3-4W
- Dimension (W*D*H*T):
188mm*189mm*162mm*50mm
- Operating humidity: 10~95%
- Operating temperature: -10~50°C (+14~122°F)

Management

- Configuration: browser/phone/auto-provision
- Auto provision via FTP/TFTP/HTTP/HTTPS for mass deploy
- Auto-provision with PnP
- Zero-sp-touch, TR-069
- Phone lock for personal privacy protection
- Reset to factory, reboot
- Package tracing export, system log


Network and Security

- SIP v1 (RFC2543), v2 (RFC3261)
- Call server redundancy supported
- NAT traversal: STUN mode
- Proxy mode and peer-to-peer SIP link mode
- IP assignment: static/DHCP
- HTTP/HTTPS web server
- Time and date synchronization using SNTP
- UDP/TCP/DNS-SRV (RFC 3263)
- QoS: 802.1p/Q tagging (VLAN), Layer 3 ToS DSCP
- SRTP for voice
- Transport Layer Security (TLS)
- HTTPS certificate manager
- AES encryption for configuration file
- Digest authentication
- OpenVPN, IEEE802.1X
- IPv6
- LLDP/CDP/DHCP VLAN
- ICE

Package Features

- Package content:
 - Yealink SIP-T31P IP phone
 - Handset with handset cord
 - Ethernet Cable (1.5m CAT5E UTP Cable)
 - Stand
 - Quick Start Guide
 - Power Adapter (Optional)
- Qty/CTN: 10 PCS
- N.W/CTN: 9.79 kg
- G.W/CTN: 10.83 kg
- Giftbox size: 213 mm*210 mm*103 mm
- Carton Meas: 535 mm*443 mm*227 mm

Compliance



Learn More

To find out how Yealink solutions can help your organization, visit us at www.yealink.com or mail to sales@yealink.com.

About Yealink

Yealink is a global leading provider of enterprise communication and collaboration solutions, offering video conferencing service to worldwide enterprises. Focusing on research and development, Yealink also insists on innovation and creation. With the outstanding technical patents of cloud computing, audio, video and image processing technology, Yealink has built up a panoramic collaboration solution of audio and video conferencing by merging its cloud services with a series of endpoints products. As one of the best providers in more than 140 countries and regions including the US, the UK and Australia, Yealink ranks No.1 in the global market share of SIP phone shipments.

Copyright

Copyright © 2020 YEALINK(XIAMEN) NETWORK TECHNOLOGY CO., LTD.

Copyright © 2020 Yealink(Xiamen) Network Technology CO., LTD. All rights reserved. No parts of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, photocopying, recording, or otherwise, for any purpose, without the express written permission of Yealink(Xiamen) Network Technology CO., LTD.

Technical Support

Visit Yealink WIKI (<http://support.yealink.com/>) for firmware downloads, product documents, FAQ, and more. For better service, we sincerely recommend you to use Yealink Ticketing system (<https://ticket.yealink.com>) to submit all your technical issues.



YEALINK(XIAMEN) NETWORK TECHNOLOGY CO.,LTD.
Web: www.yealink.com
Addr: No.1 Ling-Xia North Road, High Tech Park,
Huli District, Xiamen, Fujian, P.R.C
Copyright©2020 Yealink Inc. All right reserved.