ProductSheet

HP PageWide XL 4700 40-in Multifunction Printer with Top Stacker and 3-year Warranty (4VW15H)

Fast, seamless printing experience with the ultimate security[1]

Get high-productivity monochrome and color speeds up to 15 D/A1 pages/min[2], easy printing and workflow efficiency with HP software, and the best network protection with HP Connection Inspector dynamic security, HP Secure Boot, and Whitelisting.[1]



Fast mono and color print, keep cost under control
Don't waste time waiting on prints—high-productivity monochrome and color speeds up to 15 D/A1 pages/min.[2]

Enhanced print/scan/copy for extreme simplicity[8]
Easy printing and workflow efficiency with HP Click, HP SmartStream software; HP SmartTracker cost control.

World class printer protection with HP Wolf Pro Security
Best network protection with HP Connection Inspector dynamic security, HP Secure Boot, and Whitelisting.[1]

Specifications

Print quality color (best)	1200 x 1200 dpi
Scanner advanced features	Live preview, scan quicksets, smart background removal, black enhancement, automatic de-skew, reduce scan speed, post-edit settings (contrast, brightness, rotation, cropping and skew)
Connectivity, standard	Gigabit Ethernet (1000Base-T), USB 2.0 host
Energy star certified	Yes
Scan file format	JPG, TIFF, multi-TIFF, PDF, PDFA, multi-PDF, muli-PDFA
Scan input modes	Printer storage, USB drive, network folder (SMB), My home folder, scan to email, scan to HP SmartStream software
Scanner type	36-in (91-cm) CIS scanner
Minimum dimensions (W x D x H)	1955 x 785 x 1414 mm
Minimum dimensions (W x D x H)	77 x 30.9 x 55.7 in
Weight	452 kg
Weight	996 lb
Power consumption	0.27 kW (typical); 0.7 kW (max printing); 95 W (ready); <16 W (sleep)
Environmental certification	ENERGY STAR, EPEAT Registered, UL 2801 ECOLOGO, CE marking (including RoHS, WEEE, REACH). In compliance with WW RoHS materials restriction requirements in China, Korea, India, Vietnam, Turkey, Serbia, and Ukraine
Manufacturer Warranty	3 years

Top Recommended Displays, Accessories and Services

HP PageWide XL Supplies

HP 864 500-ml Black PageWide XL Ink Cartridge	3ED86A
HP 865 500-ml Cyan PageWide XL Ink Cartridge	3ED85A
HP 865 500-ml Magenta PageWide XL Ink Cartridge	3ED83A
HP 865 500-ml Yellow PageWide XL Ink Cartridge	3ED84A

Messaging Footnotes

[1] Based on comparison of published security specifications commissioned by HP and performed by Sogeti in September, 2020. Comparison of the HP PageWide XL portfolio and competitors that represent the majority market share of LED and UV-gel printers worldwide as of 2019 according to IDC. Comparison matrix and further details available upon request.

[2] The HP PageWide XL 4700 Printer series delivers 15 CAD output D/A1 prints in 1 minute. Number of pages will vary depending on the print mode and application printed.

[8] Multifunction capabilities are available on the HP PageWide XL 4700 Multifunction Printer only.

Technical Specifications Footnotes

No Technical Specifications Footnotes

Learn more at
hp.com

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.