



# HP E24u G4 FHD USB-C Monitor (189T0AA)

## Overview



### Enhance your viewing experience and power your PC

Enjoy an enhanced viewing experience and make the most of your desk space by charging your PC with a single USB-C® cable straight from your monitor. Work comfortably through your day on the HP E24u G4 FHD USB-C Monitor, with optimized ergonomics, HP Eye Ease, and Full HD resolution. Make life easy for IT with remote manageability[1].

### Single connection that charges your PC

Clear the cord clutter by connecting your accessories via the integrated USB hub and charge your laptop with a single USB-C® cable. Single power-on means you turn on both the monitor and laptop at the touch of a button[2].

### Personalize your view

Find your most comfortable viewing angle with 4-way ergonomic adjustability. See more of your work on the 3-sided micro-edge, 23.8-inch diagonal screen and get crisp visuals in Full HD resolution.

### Total comfort begins with HP Eye Ease

Experience exceptional vibrancy and work comfortably through your day with HP Eye Ease, the always on low blue light filter that reduces blue light exposure with zero impact to true color accuracy.

### Responsibly Made

Make a conscious choice with this monitor that's been built with the environment in mind. Its plastics consist of over 80% recycled materials[3] plus it has 100% sustainably sourced and recyclable packaging[4]. It is ENERGY STAR® certified and EPEAT® registered[5].

# Features

## All the ports you need

Connect devices with four USB ports or HDMI and easily daisy-chain additional monitors with DisplayPort™.<sup>[6]</sup>

## HP Display Center for personalization and protection

Protect your monitor from theft with the intuitive HP Display Center software that lets you personalize your settings, partition screens, and dim the screen if your monitor is disconnected without approval.<sup>[8]</sup>

## Works With Chromebook Certified

The Works With Chromebook badge on a device means it's optimized to work with your Chromebook and other Chrome OS devices. Enjoy a seamless experience across Works With Chromebook certified accessories.<sup>[10,11]</sup>

## Easily mount your Mini

Mount your HP Desktop Mini PC directly on the column stand using the optional HP B300 PC Mounting Bracket for a clutter-free workspace.<sup>[7,9]</sup>

## Add optional audio

Customize a total solution with the HP S101 Speaker Bar which attaches easily to the lower bezel to add stereo audio on your monitor.<sup>[9]</sup>

## 3-year limited warranty

3-year limited warranty includes technical support, diagnostic services, and hardware replacement.

---

[1] HP Display Manager software agent must be running on a web server and host PC. Some limitations may apply to legacy monitors.

[2] Power delivery through USB-C® up to 65 watts.

[3] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT standard.

[4] 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic. Excludes plastic bags and plastic foam sheeting.

[5] Based on US EPEAT® registration according to IEEE 1680.1-2020 EPEAT®. Status varies by country. Visit [www.epeat.net](http://www.epeat.net) for more information.

[6] HDMI and DisplayPort™ cables sold separately.

[7] Mounting hardware sold separately.

[8] Requires Windows 10 on host PC.

[9] Sold separately.

[10] Google tested to meet Chromebook compatibility standards.

[11] The Works With Chromebook badge on a device means it's optimized to work with your Chromebook and other Chrome OS devices. Enjoy a seamless experience across Works With Chromebook certified accessories.



## Specifications

<b>Display size (diagonal)</b>	23.8"
<b>Panel technology</b>	IPS
<b>Display size (diagonal)</b>	60.45 cm (23.8")
<b>Aspect ratio</b>	16:9 <sup>[1]</sup>
<b>Native resolution</b>	FHD (1920 x 1080) <sup>[1]</sup>
<b>Resolutions supported</b>	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
<b>Pixel pitch</b>	0.274 mm
<b>Brightness</b>	250 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	5ms GtG (with overdrive) <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	53.94 x 4.7 x 32.33 cm (Without stand.)
<b>Minimum dimensions (W x D x H)</b>	21.24 x 1.85 x 12.73 in (Without stand.)
<b>Dimensions With Stand (W x D x H)</b>	53.94 x 20.7 x 49.49 cm
<b>Weight</b>	6.3 kg (With stand.)
<b>Weight</b>	13.89 lb (With stand.)
<b>Display features</b>	Language selection; On-screen controls; Pivot rotation; Single Power ON; Anti-glare; Height adjustable; Works With Chromebook Certified
<b>Display Input Type</b>	1 USB Type-C™ (Alternative mode DisplayPort™ 1.2, power delivery up to 65 W); 1 DisplayPort™ 1.2-out (with HDCP support); 1 HDMI 1.4 (with HDCP support); 1 DisplayPort™ 1.2 in (with HDCP support); 4 USB-A 3.2 Gen 1
<b>Onscreen controls</b>	Exit; Information; Management; Power control; Input control; Menu control; Brightness+; Image; Color
<b>Display colors</b>	Up to 16.7 million colors supported (through FRC technology)
<b>Display scan frequency (horizontal)</b>	30-80 KHz
<b>Display scan frequency (vertical)</b>	50-60 Hz
<b>Camera</b>	No integrated camera
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	131 W (maximum), 22 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% non-condensing

<b>Sustainable impact specifications</b>	Arsenic-free display glass; Low halogen; Mercury-free display backlights; TCO Certified; TCO Certified Edge
<b>Certifications and compliances</b>	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; ENERGY STAR®; FCC; GS Mark; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV-S; UL/CSA; VCCI; Vietnam MEPS; WEEE; ISC; WW application; ICE; UAE
<b>Physical security</b>	Security lock-ready <sup>[2]</sup>
<b>Management Software</b>	HP Display Center; HP Display Manager
<b>UPC number</b>	(A2K) 195122123918; (A2N) 195122123925; (AB0) 195122123932; (AB1) 195122123949; (AB2) 195122123956; (AB4) 195122123963; (ABA) 195122123970; (ABB) 195122123987; (ABG) 195122123994; (ABJ) 4580511760724; (ABT) 195122124014; (ABU) 195122124021; (ABV) 195122124038; (ABY) 195122124045; (ACJ) 195122124090; (ACQ) 195122124120; (AKL) 195122124144; (AR6) 195122124168; (UUF) 195122124175; (UUZ) 195122124205
<b>What's in the box</b>	Monitor; USB Type-C™ cable; QSP; Doc-kit; AC power cord <sup>[4]</sup>

## Additional specifications

<b>Backlight type</b>	Edge-lit
<b>Bezel</b>	3-sided micro-edge
<b>Card reader</b>	No
<b>Color gamut</b>	72% NTSC
<b>Curvature</b>	Flat
<b>Detachable stand</b>	Yes
<b>Display area (imperial)</b>	20.75 x 11.67 in
<b>Display area (metric)</b>	52.7 x 29.65 cm
<b>Display contrast ratio (dynamic)</b>	5000000:1
<b>DisplayPort™</b>	1 DisplayPort™ 1.2
<b>DisplayPort™ Out</b>	1 DisplayPort™ 1.2-out
<b>Ethernet</b>	No
<b>Flicker-free</b>	Yes
<b>HDCP</b>	Yes, DisplayPort™ and HDMI
<b>HDMI</b>	1 HDMI 1.4
<b>Hardness</b>	3H
<b>Height adjustment range</b>	150 mm
<b>Horizontal viewing angle</b>	178°
<b>Integrated privacy filter</b>	No
<b>Low blue light</b>	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
<b>Microphone</b>	No
<b>Non-Operating Humidity Range</b>	5 - 95%
<b>Operating temperature range</b>	41 to 95°F
<b>Package dimensions (W x D x H)</b>	24.06 x 8.78 x 15.43 in
<b>Package dimensions (W x D x H)</b>	61.1 x 22.3 x 39.2 cm
<b>Package weight</b>	8.89 kg
<b>Package weight</b>	19.56 lb
<b>Panel bit depth</b>	8 bit (6 bit + 2 FRC)
<b>Pixels per inch (ppi)</b>	93 ppi
<b>Power supply type</b>	Internal
<b>Product dimensions with stand (W x D x H)</b>	21.24 x 8.15 x 19.48 in
<b>Recommended resolution</b>	FHD (1920 x 1080 @ 60 Hz)
<b>Resolution (maximum)</b>	FHD (1920 x 1080 @ 60 Hz)

<b>Screen treatment</b>	Anti-glare
<b>Speakers</b>	No
<b>Tilt</b>	-5 to +23°
<b>Touch-enabled</b>	Not touch-enabled
<b>UNSPSC code</b>	43211902
<b>USB Type-A</b>	4 SuperSpeed USB Type-A 5Gbps signaling rate
<b>USB Type-C® video input</b>	1 SuperSpeed USB Type-C® 5Gbps signaling rate (up to 65W USB Power Delivery, Alt Mode DisplayPort™ 1.2)
<b>VESA mounting</b>	100 mm x 100 mm
<b>Vertical viewing angle</b>	178°
<b>pivot</b>	±90
<b>swivel</b>	±45°

---

*[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.*

*[2] Lock sold separately.*

*[4] Included cables may vary by country.*

---

## Accessories

### Rack Brackets/Bezels/ Panels/Rails/ Trays/Mounting

★ : Recommended

#### Mounting Kits

HP B300 PC Mounting Bracket	2DW53AA
HP Single Monitor Arm	BT861AA

### Security and Protection

#### PC Locks

HP Business PC Security Lock v3 Kit	3XJ17AA
-------------------------------------	---------

### Cabinets and Stands

#### Monitor Stands

HP Integrated Work Center for Desktop Mini and Thin Client	G1V61AA
--	---------

### Audio/Multimedia and Communication Devices

#### Speakers

HP S101 Speaker Bar	5UU40AA
---------------------	---------

---

## Disclaimer — Copyright

USB-C® is a registered trademark of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR® is a registered mark owned by the U.S. government. EPEAT® is a registered trademark of GREEN ELECTRONICS COUNCIL.

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.